

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT -

BY TE CONNECTIVITY



ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED	28APR2014	T.S	N.Y
	C	REVISED PER ECR-17-018177	14DEC2017	TS	EI
	D	REVISED PER ECR-19-003686	07MAR2019	PP	JDB

2069552-1/-3
D-SHAPE TYPE I

CIRCUIT NO.





2069552-2/-4
D-SHAPE TYPE II

CIRCUIT NO.




- 1 MATERIAL AND FINISH
CONTACT
COPPER ALLOY
UNDER ALL SURFACE Ni 1.27μm MIN
TOP CONTACT AREA Au 0.5μm MIN
SOLDERING AREA Au FLASH
HOUSING
THERMO PLASTIC(UL94V-0)
SHELL
COPPER ALLOY
UNDER ALL SURFACE Ni
TOP ALL SURFACE Sn

- 2 COPLANARITY 0.1 MAX(TOP OF LEAD)
3 DIMENSION DECIDED BY CUSTOMER.



EMBOSS TAPING MSD L5	TYPE II	2069552-4
EMBOSS TAPING MSD L5	TYPE I	2069552-3
EMBOSS TAPING (SEE SHEET 2 OF 2)	TYPE II	2069552-2
EMBOSS TAPING (SEE SHEET 2 OF 2)	TYPE I	2069552-1
PACKAGING STYLE	D-SHAPE	PART NO.



RECOMMENDED BOARD DIMENSION
(CONNECTOR SIDE) ±1.6
TOLERANCE ±0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. INOMATA 12NOV2008

CHK I. HASAGAWA 12NOV2008

APVD I. HASAGAWA 12NOV2008


PRODUCT SPEC

108-78405

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.2

MATERIAL



FINISH



TE Connectivity

NAME

INDUSTRIAL MINI I/O CONN.
1.27MM PITCH 8P HDR ASSY
EMBOSS TAPING

SIZE

A3

CAGE CODE

-

DRAWING NO

C-2069552

RESTRICTED TO

-

SCALE 3:1

SHEET 1 OF 2

REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2069552-2](#)