



1 CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 .000030 MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF .200 MIN OVER .000050 MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENTAL APPLICATIONS.)

OBSOLETE	NO	YES	TIN		.130	1-207303-7
	NO	YES	TIN		.119	1-207303-6
	NO	NO	TIN	TIN	.220	1-207303-5
	NO	YES	TIN		.220	1-207303-4
	NO	NO	TIN		.220	1-207303-3
	OBSOLETE	YES	NO	TIN-LEAD		.220
BY 1-207303-4	NO	YES	TIN-LEAD	GOLD	.220	1-207303-1
	NO	NO	TIN-LEAD		.220	207303-3
	NO	NO	TIN-LEAD	TIN	.220	207303-1
	PERIPHERAL SEAL	THREADED INSERTS	CONTACT POST FINISH	CONTACT BODY FINISH	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 7-2-91 CHK W.G.LENKER 4-14-92		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 2°		NAME RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 17-16, CPC	
MATERIAL SEE CALLOUT		FINISH SEE TABLE		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		PRODUCT SPEC 108-10024		DRAWING NO C-207303	
		APPLICATION SPEC -		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE 2:1 SHEET 1 OF 1 REV V	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-207303-5](#)