


1. INSERTION/EXTRACTION TOOL AMP P/N 91067-1.	PRELIMINARY NOT RELEASED FOR PROD.	3	.018 [0.46]	.707 [17.96]	.410 [10.41]	2-207683-0
		3	.018 [0.46]	.665 [16.89]	.368 [9.35]	1-207683-8
3 FINISH: .000050 [0.00127] MIN THK GOLD PLATED PER ASTM-B-488, TYPE 3, CODE C, CLASS 1.25 OVER .000100 [0.00254] TO .000150 [0.00381] THK COPPER PER MIL-C-14550, CLASS IV.	PRELIMINARY NOT RELEASED FOR PROD.	3 10	.018 [0.46]	.760 [19.30]	.460 [11.68]	1-207683-4
		3 10	.018 [0.46]	.860 [21.84]	.560 [14.22]	1-207683-3
4 FINISH: .000050 [0.00127] MIN THK GOLD PLATED PER ASTM-B-488, TYPE 3, CODE C, CLASS 1.25 OVER .000050 [0.00127] TO .000150 [0.00381] THK NICKEL PER QQ-N-290.	PRELIMINARY NOT RELEASED FOR PROD.	3	.025 [0.64]	.860 [21.84]	.560 [14.22]	1-207683-2
		5	.018 [0.46]	.760 [19.30]	.460 [11.68]	1-207683-1
5 FINISH: .000050 [0.00127] MIN THK GOLD PLATED PER ASTM-B-488, TYPE 3, CODE C, CLASS 1.25 OVER .000200 [0.00508] TO .000250 [0.00635] THK NICKEL PER QQ-N-290.	PRELIMINARY NOT RELEASED FOR PROD.	4	.018 [0.46]	1.107 [28.12]	.810 [20.57]	207683-9
		4	.025 [0.64]	.860 [21.84]	.560 [14.22]	207683-8
6. CONTACTS MEET ALL APPLICABLE PERFORMANCE REQUIREMENTS OF MIL-C-39029.	PRELIMINARY NOT RELEASED FOR PROD.	3	.018 [0.46]	.760 [19.30]	.460 [11.68]	207683-6
		3	.018 [0.46]	1.107 [28.12]	.810 [20.57]	207683-4
7 GOTHIC "A" LOCATED APPROX AS SHOWN.	PRELIMINARY NOT RELEASED FOR PROD.	3	.018 [0.46]	.860 [21.84]	.560 [14.22]	207683-2
		FINISH	∅ "C"	"B"	"A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. ALEXANDER 11-11-91	TE TE Connectivity	
		CHK F. KINSEY 11-19-91		
DIMENSIONS: INCHES [mm]		APVD F. KINSEY 11-19-91	NAME PIN CONTACT, POSTED SIZE 22D	
		PRODUCT SPEC —		
		APPLICATION SPEC —	SIZE CAGE CODE DRAWING NO RESTRICTED TO	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[207683-2](#)