






REVISIONS						
P	LTR	DESCRIPTION	DATE	DWN	REV	APVD
J		REVISED PER ECO-17-011181	03AUG2017	RS		MZ
K		REVISED PER ECO-18-000439	19JAN2018	RS		MZ
L		REVISED PER ECO-20-002045	13FEB2020	RK		MZ

NOTES:

- 1 MATES WITH PLUG 207019-1.
- 2 CIRCUITS 1 THUR 8 COMMONED, 9 THRU 16 COMMONED, 17 THRU 24 COMMONED, 25 THRU 32 COMMONED AND 33 THRU 36 COMMONED TOGETHER.
- 3 ALL CURCUITS COMMONED TOGETHER.
- 4 TIN-LEAD OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 5 0.76 μ m (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81 μ m (.000150) MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27 μ m (.000050) MIN NICKEL PER QQ-N-290.
- 6 TIN OVER NICKEL PER QQ-N-290 OR COPPER PER MIL-C-14550.
- 7 0.76 μ m (.000030) MIN GOLD PER MIL-G-45204 FOR A LENGTH OF 5.08 (.200) FROM MATING END, 3.81 μ m (.000150) MIN TIN PER MIL-T-10727 FOR A LENGTH OF 4.83 (.190) MIN. FROM OPPOSITE END, BOTH OVER 1.27 μ m (.000050) MIN NICKEL PER QQ-N-290.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	7	(1) 36 POSITION	3	1-208062-1
	2	(1) 4 POSN AND (4) 8 POSN	2	1-208062-0
	6	(1) 36 POSITION	3	208062-9
OBSOLETE	6	(1) 4 POSN AND (4) 8 POSN	2	208062-8
	5	(1) 36 POSITION	3	208062-7
	5	(1) 4 POSN AND (4) 8 POSN	2	208062-6
OBSOLETE	4	(1) 36 POSITION	3	208062-3
	4	(1) 4 POSN AND (4) 8 POSN	2	208062-1
FINISH		BUS TYPE		PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D.GELTZ CHK R.STONE APVD	08/13/92 9-21-92	 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC ± -		PRODUCT SPEC				
		1 PLC ± -		APPLICATION SPEC				
		2 PLC ± 0.25[.010]						
		3 PLC ± -						
		4 PLC ± -		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS		WEIGHT —		A1 00779  208062		—
CUSTOMER DRAWING				SCALE 2:1		SHEET 1 OF 1		REV L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[208062-8](#)