




ELECTRICAL	MECHANICAL	ENVIRONMENTAL
IMPEDANCE <u>50 Ohm</u> FREQUENCY RANGE <u>DC to 6GHz</u> INSERTION LOSS: <u>Max. 0.05*SQRT(F) dB</u> VSWR: <u>Max. 1.15@0-3GHz</u> <u>Max. 1.20@3-6GHz</u> DIELECTRIC WITHSTAND VOLTAGE: <u>Max. 1500 V RMS</u> INSULATION RESISTANCE <u>Min. 5000 Mohms</u> PIM3: <u>Max. -160dBc @2x20W, 900MHz, 1800MHz,</u> <u>2100MHz tested with cable</u>	MATING CYCLES: <u>MIN. 100 CYCLES</u> RECOMMENDED TORQUE: <u>5Nm</u> CABLE PULLING: <u>150N MIN.</u> CABLE TORSION: <u>0.06Nm MIN.</u>	TEMPERATURE RANGE: <u>-40°~+85°C</u> SALT SPRAY: <u>96H</u> INTERFACE SEAL: <u>IP68(1m, 24h) MATED</u> PANEL SEAL: <u>N/A</u>

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD




RECOMMENDED CABLE DIMENSION




NOTE:

- 1. INTERFACE ACCORDING TO IEC 61169-54
- 2. CENTER CONTACT WITH AN INSULATOR, AND CLIP, ARE SPARE PARTS, AND WILL BE PACKAGED SEPARATELY IN BAG


P/N	PART NAME	MATERIAL	PLATING
2081974-1	CENTER CONTACT	BRONZE	SILVER
	OUTER CONTACT	BRONZE	SILVER
	BODY	BRASS	WHITE BRONZE
	INSULATOR	PTFE	
	CLIP	PTFE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JZ 10MAR2020	TE TE Connectivity					
DIMENSIONS: mm		CHK RZ 10MAR2020						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±°	APVD RS 10MAR2020	NAME 4.3-10 STRAIGHT JACK FOR 380 CABLE SOLDER TYPE, 4 HOLES SQUARE FLANGE					
		PRODUCT SPEC 108-115175						
		APPLICATION SPEC 408-160018	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
		MATERIAL SEE TABLE -	FINISH SEE TABLE -	WEIGHT 41g	A3	00779		C-2081974
CUSTOMER DRAWING			SCALE	1:1	SHEET	1 OF 2	REV	A


P	LTR	DESCRIPTION	DATE	DWN	APVD



TRAY PACKAGE




OUTER BOX (210PCS/BOX)



PACKAGE

(BOX SIZE ONLY FOR REFERENCE, UNIT: CM)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JZ	10MAR2020	 TE Connectivity													
		CHK RZ	10MAR2020														
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD RS	NAME 4.3-10 STRAIGHT JACK FOR 380 CABLE SOLDER TYPE, 4 HOLES SQUARE FLANGE												
		PRODUCT SPEC 108-115175		SIZE A3			CAGE CODE 00779		DRAWING NO C-2081974		RESTRICTED TO -						
		APPLICATION SPEC 408-160018															
		WEIGHT 41g															
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±															
MATERIAL SEE TABLE -		FINISH SEE TABLE -		CUSTOMER DRAWING								SCALE 1:1		SHEET 2 OF 2		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2081974-1](#)