





D





SECTION B-B
SHOWN WITH CPA (WHEN APPLICABLE)
IN IT'S LATCHED POSITION
FOR REFERENCE ONLY




SECTION A-A




SECTION A-A
SHOWN WITH TPA
IN IT'S LATCHED POSITION
FOR REFERENCE ONLY





WIRE CRIMP
DIMENSIONS



INSULATION CRIMP
DIMENSIONS




SECTION B-B




ISOMETRIC VIEWS
SCALE 2:1


KEYING
CONFIGURATIONS




KEYING OPTION A



KEYING OPTION B



KEYING OPTION C



KEYING OPTION D

- PART NUMBER 2098559-5 SHOWN ON DRAWING.
- TPA AND CPA (WHEN APPLICABLE) ARE SHIPPED IN THEIR PRE-LATCHED POSITIONS. SEE INSTRUCTION SHEET 408-8968 FOR DIRECTIONS ON MOVING THE CPA AND TPA TO THE PRE-LATCHED POSITION, IF NECESSARY.
- TERMINALS SOLD SEPARATELY. FOR USE WITH TE MCON 1.2mm CLEAN BODY CONTACT WITH WIRE SEAL. SEE TE MCON 1.2-CB (CLEAN BODY) TABLE FOR APPLICABLE PART NUMBERS.
- APPLICABLE HEADER INTERFACE DRAWING 114-18679-3 IS AVAILABLE UPON REQUEST. A COPY OF THIS DRAWING CAN BE OBTAINED FROM THE TE CONNECTIVITY PRODUCT MANAGER, VIA YOUR TE CONNECTIVITY SALES REPRESENTATIVE OR CUSTOMER SERVICE.
- MINIMUM FEED THROUGH CONDITION WITH 1.0mm CLEARANCE ALL AROUND.
- TRACEABILITY CODE (YY = TWO DIGIT YEAR, JJJ = 3 DIGIT JULIAN DAY, S = 1 DIGIT SHIFT) AND TE ASSEMBLY PART NUMBER PRINTED IN THIS LOCATION AT ASSEMBLY.
- NOTE DELETED.
- VALIDATED UP TO USCAR-2 TEMPERATURE CLASS IV.
- TPA ENGAGE FORCE: PRESET TO FULL ≥ 3 N AND ≤ 60 N.
- TPA DISENGAGE FORCE: DISENGAGE FROM FULL TO PRESET ≥ 6 N AND ≤ 60 N.
- CPA ENGAGE FORCE: PRESET TO FULL WITHOUT CONNECTORS MATED ≥ 40 N.
- CPA ENGAGE FORCE: PRESET TO FULL WITH CONNECTORS MATED < 30 N.
- POLARIZATION FEATURE EFFECTIVENESS:
CONNECTOR MATED TURNED 180° NO MATING > 150 N.
WRONG KEYING NO MATING > 150 N.
- SEE INSTRUCTION SHEET 408-8928

- ICD IS DEPENDENT UPON WIRE INSULATION TYPE AND OD. MUST BE SUFFICIENT TO GRIP SEAL SO IT DOES NOT SLIDE OUT OF INSULATION CRIMP WHEN INSERTING INTO CONNECTOR CAVITY BUT NOT TEAR THE SEAL.
- CAVITIES WITH A NUMBER INDICATE A CLOSED TERMINAL LOCATION. BLANK CAVITIES INDICATE OPEN TERMINAL LOCATION.
- REFERENCE ISOMETRIC VIEWS ON SHEET 2.



MAX TEMP	FEMALE TERMINAL PN	TERMINAL PLATING	AWG	APPLICABLE WIRE FINISHED O.D.	W.C.H.	W.C.W.	I.C.D.	WIRE SEAL PART NUMBER
125C	1670146-1	TIN	20	1.40 - 1.90mm	0.84 $\pm$ 0.03	1.57 $\pm$ 0.05	3.25 $\pm$ 0.05	967067-1
125C	1670146-2	GOLD	20	1.40 - 1.90mm	0.84 $\pm$ 0.03	1.57 $\pm$ 0.05	3.25 $\pm$ 0.05	967067-1
125C	1670146-3	SILVER	20	1.40 - 1.90mm	0.84 $\pm$ 0.03	1.57 $\pm$ 0.05	3.25 $\pm$ 0.05	967067-1
125C	1418850-1	TIN	18	1.90 - 2.40mm	1.11 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
125C	1418850-1	TIN	16	1.90 - 2.40mm	1.31 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
125C	1418850-2	GOLD	18	1.90 - 2.40mm	1.11 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
125C	1418850-2	GOLD	16	1.90 - 2.40mm	1.31 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
125C	1418850-3	SILVER	18	1.90 - 2.40mm	1.11 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
125C	1418850-3	SILVER	16	1.90 - 2.40mm	1.31 $\pm$ 0.05	1.78 $\pm$ 0.05	3.35 $\pm$ 0.05	964972-1
150C	1670146-2	GOLD	20	1.40 - 1.90mm	0.84 $\pm$ 0.03	1.57 $\pm$ 0.05		2098582-1
150C	1670146-3	SILVER	20	1.40 - 1.90mm	0.84 $\pm$ 0.03	1.57 $\pm$ 0.05		2098582-1
150C	1418850-2	GOLD	18	1.40 - 1.90mm	1.11 $\pm$ 0.05	1.78 $\pm$ 0.05		2098582-1
150C	1418850-2	GOLD	16	1.40 - 1.90mm	1.31 $\pm$ 0.05	1.78 $\pm$ 0.05		2098582-1
150C	1418850-3	SILVER	18	1.40 - 1.90mm	1.11 $\pm$ 0.05	1.78 $\pm$ 0.05		2098582-1
150C	1418850-3	SILVER	16	1.40 - 1.90mm	1.31 $\pm$ 0.05	1.78 $\pm$ 0.05		2098582-1

RELEASED	2138907-1							NATURAL/BROWN	D	4-2098559-4
RELEASED	1488787-1				4	3		NATURAL/BROWN	D	1-2098559-2
PRELIMINARY	1488787-1	6	5					NATURAL/BROWN	D	1-2098559-0
RELEASED	1488787-1							NATURAL/BROWN	D	2098559-8
RELEASED	N/A							NATURAL/BROWN	D	2098559-4
STATUS	CPA 	6	5	4	3	2	1	COLOR	KEY	PART NUMBER
		INNER HOUSING TERMINAL CAVITY CONFIGURATION 					INNER HOUSING			
RELEASED	2138907-1							NATURAL/BROWN	C	4-2098559-3
RELEASED	1488787-1							NATURAL/BROWN	C	2098559-7
RELEASED	N/A							NATURAL/BROWN	C	2098559-3
STATUS	CPA 	6	5	4	3	2	1	COLOR	KEY	PART NUMBER
		INNER HOUSING TERMINAL CAVITY CONFIGURATION 					INNER HOUSING			
RELEASED	2138907-1							NATURAL/BROWN	B	4-2098559-2
PRELIMINARY	1488787-1				4	3		NATURAL/BROWN	B	1-2098559-1
PRELIMINARY	1488787-1	6	5					NATURAL/BROWN	B	2098559-9
RELEASED	1488787-1							NATURAL/BROWN	B	2098559-6
RELEASED	N/A							NATURAL/BROWN	B	2098559-2
STATUS	CPA 	6	5	4	3	2	1	COLOR	KEY	PART NUMBER
		INNER HOUSING TERMINAL CAVITY CONFIGURATION 					INNER HOUSING			
RELEASED	2138907-1							NATURAL/BROWN	A	4-2098559-1
RELEASED	1488787-1							NATURAL/BROWN	A	2098559-5
RELEASED	N/A							NATURAL/BROWN	A	2098559-1
STATUS	CPA 	6	5	4	3	2	1	COLOR	KEY	PART NUMBER
		INNER HOUSING TERMINAL CAVITY CONFIGURATION 					INNER HOUSING			

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	S. VINAY	07OCT2009		TE Connectivity								
DIMENSIONS:	mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	B. BUCHTER	07OCT2009										
				APVD	B. BUCHTER	07OCT2009										
				PRODUCT SPEC												
MATERIAL	SEE TABLE		FINISH	APPLICATION SPEC			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO						
				SEE NOTES												
				WEIGHT		5.53 grams										
CUSTOMER DRAWING				A100779C=2098559				SCALE		SHEET 1 OF 2	REV A					
								4:1								

REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-

ISOMETRIC VIEWS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. VINAY	07OCT2009	TE Connectivity	
DIMENSIONS:		CHK B. BUCHTER	07OCT2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B. BUCHTER	07OCT2009	NAME	
	0 PLC	±		CONNECTOR ASSEMBLY, FEMALE, 6 POSITION, SEALED, 1.2mm MCON HIGH TEMP	
	1 PLC	±0.3			
	2 PLC	±0.10			
	3 PLC	±			
	4 PLC	±		SIZE	
	ANGLES	±1°			
MATERIAL	FINISH			CAGE CODE	
SEE TABLE	-			DRAWING NO	
		WEIGHT	5.53 grams	RESTRICTED TO	
		CUSTOMER DRAWING		A100779C=2098559	
		SCALE	4:1	SHEET 2 OF 2	
				REV A4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2098559-6](#)