


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-21-103323	19MAY2021	NT	JDB
	A1	ECR-17-001194	31JAN2017	RK	PFR



NOTES:

- PACKAGING: ACC. TO TE SPEC. 107-18064
- ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.
SHORT-CIRCUIT AND CONTINUITY TEST AT 500V DC, 0.1s
- KEEP THE DIRECTION OF CONNECTOR TO THE CABLE ON BOTH SIDE THE SAME
- WIRING SCHEMA ACC. TO TIA/EIA-568-B AS SHOWN IN WIRING SCHEDULE
- PROP 65 WARNING LABEL: SEE SHEET 2
- LABEL TEXT:
TE CONNECTIVITY
WW/YY/PRODUCTION LOCATION CODE

WIRING SCHEDULE

CAVITY SIDE A	COLOR	CAVITY SIDE B
1	WH/OG	1
2	OG	2
3	WH/GN	3
4	BU	4
5	WH/BU	5
6	GN	6
7	WH/BN	7
8	BN	8

5	10000 (±300)	HiFlex MultiPurpose 70°C PUR	2-2205133-6
	5000 (±150)	HiFlex MultiPurpose 70°C PUR	2-2205133-5
	3000 (±50)	HiFlex MultiPurpose 70°C PUR	2-2205133-4
	2000 (±25)	HiFlex MultiPurpose 70°C PUR	2-2205133-3
	1000 (±15)	HiFlex MultiPurpose 70°C PUR	2-2205133-2
	500 (±10)	HiFlex MultiPurpose 70°C PUR	2-2205133-1
OBSOLETE	10000 (±300)	HI 125°C TPE	1-2205133-6
	5000 (±150)	HI 125°C TPE	1-2205133-5
	3000 (±50)	HI 125°C TPE	1-2205133-4
	2000 (±25)	HI 125°C TPE	1-2205133-3
	1000 (±15)	HI 125°C TPE	1-2205133-2
	500 (±10)	HI 125°C TPE	1-2205133-1
	10000 (±300)	STD 110°C PVC	2205133-6
	5000 (±150)	STD 110°C PVC	2205133-5
	3000 (±50)	STD 110°C PVC	2205133-4
	2000 (±25)	STD 110°C PVC	2205133-3
	1000 (±15)	STD 110°C PVC	2205133-2
	500 (±10)	STD 110°C PVC	2205133-1
Length "L"		Cable version	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± 1°

FINISH
-

DWN 05FEB2015
SATHISH KUMAR .G

CHK 05FEB2015
B.VELDHoven

APVD 05FEB2015
A.VAN ZANDVOORT

PRODUCT SPEC
108-78955

APPLICATION SPEC
114-5506

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME
CA MINI IO TYPE I IND RJ45

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=2205133

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 2

REV
A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2205133-4](#)