









SINGLE POLARIZATION



PANEL CUTOUT



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

- DWV RATING: 725VAC @ SEA LEVEL
- WIRE SIZE: 28 AWG MAX
- WORKING TEMPERATURE: -55°C ~ +125°C

4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK
O RING : SILICON RUBBER

5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM

- WATER PROOF: 1M IMMERSION

7 PART IS MARKED WITH TE PART NUMBER, CHINA, DATE CODE AND LOT ID

8 ALL TOLERANCES +/-0.20 UNLESS NOTED.

5	CHROMIUM-BLACK	DOUBLE	SOLDER CUP	2101677-2
5	CHROMIUM-BLACK	SINGLE	SOLDER CUP	2101677-1
SHELL SIZE	FINISH	POLARIZATION	TERMINATION	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 03MAR2010	 TE Connectivity	
DIMENSIONS: mm		CHK R. GROSS 03MAR2010	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. GROSS 03MAR2010	PRODUCT SPEC	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2101677-2](#)