

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A20	REVISED PER ECR-20-016246	07DEC2020	MM	JL
			A21	REVISED PER ECR-21-110497	17AUG2021	JL	MM

NOTES:

1. MATERIALS:
HOUSING: GLASS-FILLED THERMOPLASTIC, UL 94V-0 RATED DIMMING
CONTACTS (2 OR 4) AND LINE VOLTAGE CONTACTS (3): COPPER ALLOY

2.FINISH:
DIMMING CONTACTS (2 OR 4): NICKEL UNDERPLATE ENTIRE CONTACT
0.127 μ m MIN THICK. GOLD PLATE CONTACT PAD AREA (MATING FACE
SIDE ONLY) 0.76 μ m MIN THICK. MATTE TIN PLATE TAB ON BOTH SIDES
0.30 μ m MIN THICK. LINE VOLTAGE CONTACTS (3): TIN PLATE.

3 LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 150°C RATED, COPPER 41/30 STRANDED
PER UL STYLE AWM 3321.

4 MATING INTERFACE PER ANSI C136.41-2013.

 OPTIONAL DIMMING CONTACTS (2) SUPPLIED.

6 DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 150°C RATED, 16/30 STRANDED,
PER UL STYLE AWM 3321.

7 LINE VOLTAGE CONDUCTORS (3):
14 AWG, 600V, 105°C RATED, COPPER 41/30 STRANDED.
PER UL STYLE AWM 1015.


8) DIMMING CONDUCTORS (2 OR 4):
18 AWG, 600V, 105°C RATED, COPPER 16/30 STRANDED.
PER UL STYLE AWM 1015.

9 LUBRICATION: GOLD PLATED CONTACT PAD SURFACES OF DIMMING CONTACTS ARE LUBRICATED WITH A TRANSPARENT (NON-VISIBLE) LUBRICANT TO IMPROVE DURABILITY AND PERFORMANCE. AVOID CONTACT WITH THESE SURFACES WHICH MAY RESULT IN REMOVAL OF LUBRICANT


10 PRELIMINARY.

 FOR PART NUMBER 5-2213362-4 ONLY,
STRIP AND REMOVE INSULATION AS SHOWN.
LEAD WIRES TO BE SOLDER DIPPED.

12. MUST BE USED WITH EITHER GASKET P/N 2213469-1 OR P/N 2324246-1 (SOLD SEPARATELY).





SEE SHEET 2 FOR
WIRING COLOR CODE



12.0	203.0	153.0	153.0	7 AND 8	4	9-2213362-4
12.7	1036.3	1000	986.5	7 AND 8	4 5	8-2213362-4 10
12.7	266.3	230.0	216.5	7 AND 8	4 5	7-2213362-4
12.7	236.3	200.0	-	7	-	6-2213362-4 10
12.7	341.1	304.8	-	3	-	6-2213362-2
12.7	341.1	304.8	-	7	-	6-2213362-1
15.88	264.9	228.6	-	3	-	5-2213362-9
BLACK WIRE:15.88 WHITE WIRE:15.88 RED WIRE:6.35	798.3	762.0	-	3	-	5-2213362-8
9.0	341.1	304.8	291.3	7 AND 8	4 5	5-2213362-4 1 10
9.0	341.1	304.8	291.3	7 AND 8	4 5	4-2213362-5
12.7	950.7	914.4	914.4	7 AND 8	4 5	4-2213362-4 10
8.0	73.0	35.0	35.0	7 AND 8	4 5	3-2213362-4 10
12.7	1865.1	1828.8	1815.3	3 AND 6	2	3-2213362-1 10
12.7	736.3	700.0	686.5	7 AND 8	4 5	2-2213362-4
12.7	696.3	660.0	646.5	3 AND 6	4 5	2-2213362-2 10
12.7	696.3	660.0	646.5	3 AND 6	2	2-2213362-1
12.7	536.3	500.0	486.5	7 AND 8	4 5	1-2213362-4
12.7	536.3	500.0	486.5	7 AND 8	2	1-2213362-3 10
12.7	1823.3	1346.0	1332.5	3 AND 6	4 5	1-2213362-2
12.7	536.3	500.0	486.5	3 AND 6	2	1-2213362-1 10
12.7	341.1	304.8	291.3	7 AND 8	4 5	2213362-4
12.7	341.1	304.8	291.3	7 AND 8	2	2213362-3
12.7	341.1	304.8	291.3	3 AND 6	4 5	2213362-2
12.7	341.1	304.8	291.3	3 AND 6	2	2213362-1
D	C	A	B	WIRE STYLE	QUANTITY OF DIMMING CONTACTS	PART NO.
STRIP LENGTH	OVERALL LENGTH	WIRE LENGTH				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26JUN2013 J. SHAFFER CHK 26JUN2013 E. HOWARD APVD 26JUN2013 E. HOWARD		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- MATERIAL FINISH		NAME RECEPTACLE ASSEMBLY, DIMMABLE PHOTOCONTROL -	
		PRODUCT SPEC 108-32059 APPLICATION SPEC 114-32115		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
-		WEIGHT -		A200779 C-2213362 -	
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 2 REV A21	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER	26 JUN 2013		 TE Connectivity									
DIMENSIONS:		CHK E. HOWARD	26 JUN 2013		NAME RECEPTACLE ASSEMBLY, DIMMABLE PHOTOCONTROL -									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD	26 JUN 2013											
mm		PRODUCT SPEC 108-32059												
		APPLICATION SPEC 114-32115												
MATERIAL		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO						
-		-		A2		00779	C-2213362	-						
CUSTOMER DRAWING							SCALE	1:1	SHEET	2	OF	2	REV	A21

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2213362-1](#)