





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED PER ECR-21-006029	02SEP2021	VG	PO



SPECIFICATIONS



CONTACT RATING: SILVER: 3A @ 250 VAC RESISTIVE
GOLD: 0.4VA @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50 mΩ MAX @ 1A 12VDC (INITIAL VALUE)
ELECTRICAL LIFECYCLES: 50,000 MAKE AND BREAK CYCLES
AT FULL LOAD

ACTUATION FORCE: SP: 2.5±1 NEWTON, DP: 3.5±1 NEWTON
ACTUATION TRAVEL: 3.2MM
SEALED PER IP67, IK10 (STAINLESS)
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFECYCLES: MOMENTARY: 1,000,000 CYCLES
LOCKING: 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m

MATERIALS

BUSHING: STAINLESS STEEL
BASE: PBT (UL 94-V0), PC (UL 94-V2)
ACTUATOR: STAINLESS STEEL, PC
SEALING: O-RING (SILICONE)
TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED
HEX NUT: BRASS BASE, NICKEL PLATED

- 1 ALL MATERIAL AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)



EXPLODED VIEW

ASSEMBLED VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 06FEB2016	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 06FEB2016			
		APVD HILL RYAN 06FEB2016	NAME ANTI-VANDAL SWITCH 19mm FIXED RING LED		
		PRODUCT SPEC	—		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	—		
0 PLC ± -		—	SIZE A2		
1 PLC ± -		—	CAGE CODE 00779		
2 PLC ± -		—	DRAWING NO C-2213764		
3 PLC ± -		—	RESTRICTED TO —		
4 PLC ± -		—	—		
ANGLES ± -		—	—		
FINISH		WEIGHT 0	—		
—		CUSTOMER DRAWING	—		
		SCALE 1:1	SHEET 1 OF 4		
			REV B1		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

C

B


A


D

C

B

A



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 06FEB2016		 TE Connectivity																			
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 06FEB2016																					
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD HILL RYAN 06FEB2016		NAME ANTI-VANDAL SWITCH 19MM FIXED RING LED																		
	0 PLC ± -		PRODUCT SPEC																				
	1 PLC ± -		—																				
	2 PLC ± -		APPLICATION SPEC																				
MATERIAL —	3 PLC ± -		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO												
	4 PLC ± -		—		A2		00779		C=2213764		—												
	ANGLES ± -		WEIGHT —																				
	FINISH —		CUSTOMER DRAWING																				
												SCALE		1:1		SHEET		2 of 4		REV		B1	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SINGLE POLE— LOCKING	GOLD	BLUE	24V	AV1911R724R04	4—2213764—0
	SILVER	BLUE	24V	AV1911R724Q04	3—2213764—9
	GOLD	BLUE	12V	AV1911R712R04	3—2213764—8
	SILVER	BLUE	12V	AV1911R712Q04	3—2213764—7
	GOLD	GREEN	24V	AV1911R624R04	3—2213764—6
	SILVER	GREEN	24V	AV1911R624Q04	3—2213764—5
	GOLD	GREEN	12V	AV1911R612R04	3—2213764—4
	SILVER	GREEN	12V	AV1911R612Q04	3—2213764—3
	GOLD	YELLOW	24V	AV1911R524R04	3—2213764—2
	SILVER	YELLOW	24V	AV1911R524Q04	3—2213764—1
	GOLD	YELLOW	12V	AV1911R512R04	3—2213764—0
	SILVER	YELLOW	12V	AV1911R512Q04	2—2213764—9
	GOLD	RED	24V	AV1911R324R04	2—2213764—8
	SILVER	RED	24V	AV1911R324Q04	2—2213764—7
	GOLD	RED	12V	AV1911R312R04	2—2213764—6
	SILVER	RED	12V	AV1911R312Q04	2—2213764—5
	GOLD	WHITE	24V	AV1911R124R04	2—2213764—4
	SILVER	WHITE	24V	AV1911R124Q04	2—2213764—3
	GOLD	WHITE	12V	AV1911R112R04	2—2213764—2
	SILVER	WHITE	12V	AV1911R112Q04	2—2213764—1
SINGLE POLE— MOMENTARY	GOLD	BLUE	24V	AV1910R724R04	2—2213764—0
	SILVER	BLUE	24V	AV1910R724Q04	1—2213764—9
	GOLD	BLUE	12V	AV1910R712R04	1—2213764—8
	SILVER	BLUE	12V	AV1910R712Q04	1—2213764—7
	GOLD	GREEN	24V	AV1910R624R04	1—2213764—6
	SILVER	GREEN	24V	AV1910R624Q04	1—2213764—5
	GOLD	GREEN	12V	AV1910R612R04	1—2213764—4
	SILVER	GREEN	12V	AV1910R612Q04	1—2213764—3
	GOLD	YELLOW	24V	AV1910R524R04	1—2213764—2
	SILVER	YELLOW	24V	AV1910R524Q04	1—2213764—1
	GOLD	YELLOW	12V	AV1910R512R04	1—2213764—0
	SILVER	YELLOW	12V	AV1910R512Q04	2213764—9
	GOLD	RED	24V	AV1910R324R04	2213764—8
	SILVER	RED	24V	AV1910R324Q04	2213764—7
	GOLD	RED	12V	AV1910R312R04	2213764—6
	SILVER	RED	12V	AV1910R312Q04	2213764—5
	GOLD	WHITE	24V	AV1910R124R04	2213764—4
	SILVER	WHITE	24V	AV1910R124Q04	2213764—3
	GOLD	WHITE	12V	AV1910R112R04	2213764—2
	SILVER	WHITE	12V	AV1910R112Q04	2213764—1
POLE/THROW	CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06FEB2016 CHK 06FEB2016 HILL RYAN HILL RYAN APVD 06FEB2016		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ANTI-VANDAL SWITCH 19MM FIXED RING LED	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL -		FINISH -			
WEIGHT -				SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING				DRAWING NO C=2213764	RESTRICTED TO -
				SCALE 1:1	SHEET 3 of 4
				REV B1	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

DOUBLE POLE-LOCKING

DOUBLE POLE-MOMENTARY

POLE/THROW

GOLD	BLUE	24V	AV1921R724R04	8-2213764-0	
SILVER	BLUE	24V	AV1921R724Q04	7-2213764-9	
GOLD	BLUE	12V	AV1921R712R04	7-2213764-8	
SILVER	BLUE	12V	AV1921R712Q04	7-2213764-7	
GOLD	GREEN	24V	AV1921R624R04	7-2213764-6	
SILVER	GREEN	24V	AV1921R624Q04	7-2213764-5	
GOLD	GREEN	12V	AV1921R612R04	7-2213764-4	
SILVER	GREEN	12V	AV1921R612Q04	7-2213764-3	
GOLD	YELLOW	24V	AV1921R524R04	7-2213764-2	
SILVER	YELLOW	24V	AV1921R524Q04	7-2213764-1	
GOLD	YELLOW	12V	AV1921R512R04	7-2213764-0	
SILVER	YELLOW	12V	AV1921R512Q04	6-2213764-9	
GOLD	RED	24V	AV1921R324R04	6-2213764-8	
SILVER	RED	24V	AV1921R324Q04	6-2213764-7	
GOLD	RED	12V	AV1921R312R04	6-2213764-6	
SILVER	RED	12V	AV1921R312Q04	6-2213764-5	
GOLD	WHITE	24V	AV1921R124R04	6-2213764-4	
SILVER	WHITE	24V	AV1921R124Q04	6-2213764-3	
GOLD	WHITE	12V	AV1921R112R04	6-2213764-2	
SILVER	WHITE	12V	AV1921R112Q04	6-2213764-1	
GOLD	BLUE	24V	AV1920R724R04	6-2213764-0	
SILVER	BLUE	24V	AV1920R724Q04	5-2213764-9	
GOLD	BLUE	12V	AV1920R712R04	5-2213764-8	
SILVER	BLUE	12V	AV1920R712Q04	5-2213764-7	
GOLD	GREEN	24V	AV1920R624R04	5-2213764-6	
SILVER	GREEN	24V	AV1920R624Q04	5-2213764-5	
GOLD	GREEN	12V	AV1920R612R04	5-2213764-4	
SILVER	GREEN	12V	AV1920R612Q04	5-2213764-3	
GOLD	YELLOW	24V	AV1920R524R04	5-2213764-2	
SILVER	YELLOW	24V	AV1920R524Q04	5-2213764-1	
GOLD	YELLOW	12V	AV1920R512R04	5-2213764-0	
SILVER	YELLOW	12V	AV1920R512Q04	4-2213764-9	
GOLD	RED	24V	AV1920R324R04	4-2213764-8	
SILVER	RED	24V	AV1920R324Q04	4-2213764-7	
GOLD	RED	12V	AV1920R312R04	4-2213764-6	
SILVER	RED	12V	AV1920R312Q04	4-2213764-5	
GOLD	WHITE	24V	AV1920R124R04	4-2213764-4	
SILVER	WHITE	24V	AV1920R124Q04	4-2213764-3	
GOLD	WHITE	12V	AV1920R112R04	4-2213764-2	
SILVER	WHITE	12V	AV1920R112Q04	4-2213764-1	
POLE/THROW	CONTACT	LED COLOR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC±-
1 PLC±-
2 PLC±-
3 PLC±-
4 PLC±-
ANGLES±-

FINISH-

DWN06FEB2016
CHKHILL RYAN06FEB2016
APVDHILL RYAN06FEB2016
PRODUCT SPEC
APPLICATION SPEC
WEIGHT-

CUSTOMER DRAWING

06FEB2016
NAGALAKSHMI K
06FEB2016

TE Connectivity

NAME
ANTI-VANDAL SWITCH 19MM
FIXED RING LED

SIZEA2CAGE CODE00779DRAWING NOC=2213764RESTRICTED TO-

SCALE1:1SHEET4 OF 4REV B1

1471-9 (1/15)

2213764

2213764

2213764

2213764

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[AV1910R612Q04](#)