




1. MATERIAL:
BODY: ALUMINUM PER ASTM B317
INSERT: BRASS PER ASTM B36
2. FINISH:
BODY: .000600 MIN MATTE TIN PER ASTM B545
OVER .000060 MIN NICKEL PER ASTM B733.
INSERT: .000150 MIN MATTE NICKEL PER QQ-N-290
3. PTFE DRY LUBRICANT 360 DEGREE ON OUTER DIAMETER
OF CRIMP BARREL IN ZONE SHOWN.
4. WIRE INSULATION RANGE: .490-.574.
5. SEE TE CONNECTIVITY APPLICATION SPEC. 114-32098
FOR APPLICATION REQUIREMENTS.
6. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-32087
FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 3
FOR WIRE STRIPPING DETAIL.



SCALE 2:1



2102573-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN 15NOV2011	TE Connectivity	
		CHK DEBOCK, KIM 28NOV2012		
DIMENSIONS:		APVD DEBOCK, KIM 28NOV2012	NAME ASSEMBLY, ALUMINUM TERMINAL, STRAIGHT, SINGLE HOLE, 2/0	
IN		PRODUCT SPEC		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
		WEIGHT		
MATERIAL SEE CALL-OUT		CUSTOMER DRAWING	A100779C=2102573	
			SCALE 4:1	SHEET 1 OF 1
			REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2102573-1](#)