










CONTACT RATING: SILVER: 3A @ 250 VAC RESISTIVE
GOLD: 0.4VA @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50 mΩ MAX @ 1A 12VDC (INITIAL VALUE)
ELECTRICAL LIFECYCLES: 50,000 MAKE AND BREAK CYCLES
AT FULL LOAD


ACTUATION FORCE: SP: 2.5±1 NEWTON, DP: 3.5±1 NEWTON
ACTUATION TRAVEL: 3.2mm
SEALED PER IP67, IK10 (STAINLESS)
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFECYCLES: MOMENTARY: 1,000,000 CYCLES
LOCKING: 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m

BUSHING: STAINLESS STEEL
 BASE: PBT (UL 94-V0), PC (UL 94-V2)
 ACTUATOR: STAINLESS STEEL, PC
 SEALING: O-RING (SILICONE)
 TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED
 HEX NUT: BRASS BASE, NICKEL PLATED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08FEB2016 CHK <u>NAGALAKSHMI K</u> 08FEB2016 APVD <u>HILL RYAN</u> 08FEB2016		 TE Connectivity				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC ± -		- ANTI-VANDAL SWITCH 19mm POWER LOGO LED				
		1 PLC ± -						
		2 PLC ± -						
		3 PLC ± -						
4 PLC ± -		PRODUCT SPEC		SIZE				
ANGLES ± -		APPLICATION SPEC						
MATERIAL		FINISH		CAGE CODE		DRAWING NO		RESTRICTED TO
-		-		WEIGHT		0		-
				A2		00779		C=2213766
CUSTOMER DRAWING				SCALE		6:1		SHEET
						1 of 3		REV
								C


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 08FEB2016		 TE Connectivity								
		CHK HILL RYAN 08FEB2016										
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ANTI-VANDAL SWITCH 19mm POWER LOGO LED								
	0 PLC ± -		APVD HILL RYAN 08FEB2016									
	1 PLC ± -		PRODUCT SPEC									
	2 PLC ± -		—									
	3 PLC ± -		APPLICATION SPEC									
	4 PLC ± -		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
ANGLES ± -		—	WEIGHT	A2	00779	C=2213766						
MATERIAL	FINISH	—		CUSTOMER DRAWING			SCALE	NTS	SHEET	2 of 3	REV	C

4		3			2			1							
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION						REVISIONS							
© COPYRIGHT - By -		ALL RIGHTS RESERVED.						P	LTR	DESCRIPTION		DATE	DWN	APVD	
									-	SEE SHEET 1		-	-	-	
DOUBLE POLE-MOMENTARY	SILVER	WHITE	24V	AV1920P124Q04	4-2213766-3										
	GOLD	WHITE	12V	AV1920P112R04	4-2213766-2										
	SILVER	WHITE	12V	AV1920P112Q04	4-2213766-1										
SINGLE POLE-LOCKING	GOLD	BLUE	24V	AV1911P724R04	4-2213766-0										
	SILVER	BLUE	24V	AV1911P724Q04	3-2213766-9										
	GOLD	BLUE	12V	AV1911P712R04	3-2213766-8										
	SILVER	BLUE	12V	AV1911P712Q04	3-2213766-7										
	GOLD	GREEN	24V	AV1911P624R04	3-2213766-6										
	SILVER	GREEN	24V	AV1911P624Q04	3-2213766-5										
	GOLD	GREEN	12V	AV1911P612R04	3-2213766-4										
	SILVER	GREEN	12V	AV1911P612Q04	3-2213766-3										
	GOLD	YELLOW	24V	AV1911P524R04	3-2213766-2										
	SILVER	YELLOW	24V	AV1911P524Q04	3-2213766-1										
	GOLD	YELLOW	12V	AV1911P512R04	3-2213766-0										
	SILVER	YELLOW	12V	AV1911P512Q04	2-2213766-9										
	GOLD	RED	24V	AV1911P324R04	2-2213766-8										
	SILVER	RED	24V	AV1911P324Q04	2-2213766-7										
	GOLD	RED	12V	AV1911P312R04	2-2213766-6										
	SILVER	RED	12V	AV1911P312Q04	2-2213766-5										
	GOLD	WHITE	24V	AV1911P124R04	2-2213766-4										
	SILVER	WHITE	24V	AV1911P124Q04	2-2213766-3										
	GOLD	WHITE	12V	AV1911P112R04	2-2213766-2										
	SILVER	WHITE	12V	AV1911P112Q04	2-2213766-1										
	SINGLE POLE-MOMENTARY	GOLD	BLUE	24V	AV1910P724R04	2-2213766-0									
		SILVER	BLUE	24V	AV1910P724Q04	1-2213766-9									
		GOLD	BLUE	12V	AV1910P712R04	1-2213766-8									
		SILVER	BLUE	12V	AV1910P712Q04	1-2213766-7									
		GOLD	GREEN	24V	AV1910P624R04	1-2213766-6									
		SILVER	GREEN	24V	AV1910P624Q04	1-2213766-5									
		GOLD	GREEN	12V	AV1910P612R04	1-2213766-4									
		SILVER	GREEN	12V	AV1910P612Q04	1-2213766-3									
GOLD		YELLOW	24V	AV1910P524R04	1-2213766-2										
SILVER		YELLOW	24V	AV1910P524Q04	1-2213766-1										
GOLD		YELLOW	12V	AV1910P512R04	1-2213766-0										
SILVER		YELLOW	12V	AV1910P512Q04	2213766-9										
GOLD		RED	24V	AV1910P324R04	2213766-8										
SILVER		RED	24V	AV1910P324Q04	2213766-7										
GOLD		RED	12V	AV1910P312R04	2213766-6										
SILVER		RED	12V	AV1910P312Q04	2213766-5										
GOLD		WHITE	24V	AV1910P124R04	2213766-4										
SILVER		WHITE	24V	AV1910P124Q04	2213766-3										
GOLD		WHITE	12V	AV1910P112R04	2213766-2										
SILVER		WHITE	12V	AV1910P112Q04	2213766-1										
POLE/THROW	CONTACT	LED COLOUR	LED VOLTAGE	TE DESCRIPTIVE PN	TE PART NUMBER										

DOUBLE POLE-LOCKING	GOLD	BLUE	24V	AV1921P724R04	8-2213766-0			
	SILVER	BLUE	24V	AV1921P724Q04	7-2213766-9			
	GOLD	BLUE	12V	AV1921P712R04	7-2213766-8			
	SILVER	BLUE	12V	AV1921P712Q04	7-2213766-7			
	GOLD	GREEN	24V	AV1921P624R04	7-2213766-6			
	SILVER	GREEN	24V	AV1921P624Q04	7-2213766-5			
	GOLD	GREEN	12V	AV1921P612R04	7-2213766-4			
	SILVER	GREEN	12V	AV1921P612Q04	7-2213766-3			
	GOLD	YELLOW	24V	AV1921P524R04	7-2213766-2			
	SILVER	YELLOW	24V	AV1921P524Q04	7-2213766-1			
DOUBLE POLE-MOMENTARY	GOLD	YELLOW	12V	AV1921P512R04	7-2213766-0			
	SILVER	YELLOW	12V	AV1921P512Q04	6-2213766-9			
	GOLD	RED	24V	AV1921P324R04	6-2213766-8			
	SILVER	RED	24V	AV1921P324Q04	6-2213766-7			
	GOLD	RED	12V	AV1921P312R04	6-2213766-6			
	SILVER	RED	12V	AV1921P312Q04	6-2213766-5			
	GOLD	WHITE	24V	AV1921P124R04	6-2213766-4			
	SILVER	WHITE	24V	AV1921P124Q04	6-2213766-3			
	GOLD	WHITE	12V	AV1921P112R04	6-2213766-2			
	SILVER	WHITE	12V	AV1921P112Q04	6-2213766-1			
	GOLD	BLUE	24V	AV1920P724R04	6-2213766-0			
	SILVER	BLUE	24V	AV1920P724Q04	5-2213766-9			
	GOLD	BLUE	12V	AV1920P712R04	5-2213766-8			
	SILVER	BLUE	12V	AV1920P712Q04	5-2213766-7			
	GOLD	GREEN	24V	AV1920P624R04	5-2213766-6			
	SILVER	GREEN	24V	AV1920P624Q04	5-2213766-5			
	GOLD	GREEN	12V	AV1920P612R04	5-2213766-4			
	SILVER	GREEN	12V	AV1920P612Q04	5-2213766-3			
GOLD	YELLOW	24V	AV1920P524R04	5-2213766-2				
SILVER	YELLOW	24V	AV1920P524Q04	5-2213766-1				
GOLD	YELLOW	12V	AV1920P512R04	5-2213766-0				
SILVER	YELLOW	12V	AV1920P512Q04	4-2213766-9				
GOLD	RED	24V	AV1920P324R04	4-2213766-8				
SILVER	RED	24V	AV1920P324Q04	4-2213766-7				
GOLD	RED	12V	AV1920P312R04	4-2213766-6				
SILVER	RED	12V	AV1920P312Q04	4-2213766-5				
GOLD	WHITE	24V	AV1920P124R04	4-2213766-4				

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN 08FEB2016 NAGALAKSHMI K	 TE Connectivity				
	CHK 08FEB2016 HILL RYAN					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD 08FEB2016 HILL RYAN	NAME			
	PRODUCT SPEC					
MATERIAL	APPLICATION SPEC	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	-	A2	00779	C=2213766	-
CUSTOMER DRAWING			SCALE	NTS	SHEET	REV
				3 of 3		C

1471-9 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2213766-2](#)