




THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

R BROWN

20APR2009

CHK

M MOSTOLLER

20APR2009

APVD

-

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

Customer Drawing

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.2

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

MATERIAL

-

NAME

CABLE ASSEMBLY, RECEPTACLE, SLIMSEAL SSL CONNECTOR

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2106391

RESTRICTED TO

-

SCALE

4:1

SHEET

1

OF

3

REV

H

1471-9 (3/11)

D

D

C


C

B

B

A

A



2106391-3, 2106391-6, 2106391-9, 1-2106391-2, 1-2106391-5, 1-2106391-8, 2-2106391-1 and 2-2106391-4 SHOWN

2106391-3 SHOWN
(SAME AS 2106391-2
EXCEPT 3 POSITION)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R BROWN
20APR2009

CHK
M MOSTOLLER
20APR2009

APVD
-

TE Connectivity

CABLE ASSEMBLY, RECEPTACLE,
SLIMSEAL SSL CONNECTOR

SIZE
A200779

CAGE CODE
C-2106391

DRAWING NO
-

RESTRICTED TO
-

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL
-

-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

SCALE
4:1

SHEET
2

OF
3

REV
H

1471-9 (3/11)

D

D

C



C

B

B

A

A



2106391-4, 2106391-7, 1-2106391-0, 1-2106391-3, 1-2106391-6, 1-2106391-9, 2-2106391-2 and 2-2106391-5 SHOWN

2106391-4 SHOWN
(SAME AS 2106391-2
EXCEPT 4 POSITION)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R BROWN
20APR2009

CHK
M MOSTOLLER
20APR2009

APVD
-

TE Connectivity

CABLE ASSEMBLY, RECEPTACLE,
SLIMSEAL SSL CONNECTOR

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL

-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

Customer Drawing

NAME

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2106391

RESTRICTED TO
-

SCALE
4:1

SHEET
3

OF
3

REV
H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2106391-1](#)