



LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A1		REVISED PER ECR-12-003555	19APR2012	RS	DD
		A2		REVISED PER ECR-12-016877	20OCT2012	RS	DD
		B		REVISED PER ECR-15-004054	28JUL2015	RS	DD
		C		REVISED PER ECR-15-017995	18DEC2015	RS	DD

CENTER
OF GRAVITY

3.81
CENTER OF
GRAVITY



△	MATERIALS AND FINISH: - HOUSING: LCP, COLOR: NATURAL - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni	B	REVISED PER ECR
		C	REVISED PER ECR

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS).

3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.

18AWG	MAX	INSULATION	OD:	2.20
20AWG	MAX	INSULATION	OD:	1.90
22AWG	MAX	INSULATION	OD:	1.70
24AWG	MAX	INSULATION	OD:	1.45





4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION, EXCEPT 1 POSITION CONNECTOR.

5 WIRE SIZE MARKING IN APPROXIMATE LOCATION SHOWN.

△₆ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.


 COLOR CODE MARKING, STRAIGHT LINE.

8 | POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




RED	17.70	24 AWG	4	3-2106431-4
	13.70	24 AWG	3	3-2106431-3
	9.70	24 AWG	2	3-2106431-2
	5.70	24 AWG	1	 3-2106431-1
GREEN	17.70	22 AWG	4	2-2106431-4
	13.70	22 AWG	3	2-2106431-3
	9.70	22 AWG	2	2-2106431-2
	5.70	22 AWG	1	 2-2106431-1
BLUE	17.70	20 AWG	4	1-2106431-4
	13.70	20 AWG	3	1-2106431-3
	9.70	20 AWG	2	1-2106431-2
	5.70	20 AWG	1	 1-2106431-1
YELLOW	17.70	18 AWG	4	2106431-4
	13.70	18 AWG	3	2106431-3
	9.70	18 AWG	2	2106431-2
	5.70	18 AWG	1	 2106431-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DAILY 09DEC2008 CHR J DYER 09DEC2008		TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266		ASSEMBLY, IDC SSL CONNECTOR, SMT, PASS THRU	
MATERIAL		WEIGHT		SIZE	RESTRICTED TO
		-		A200779	-
		-		C-2106431	-
Customer Drawing				SCALE	REV
				8.1	3






3 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED PAD LAYOUT
SCALE 8:1

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



SECTION X-X

2106431-2 SHOWN IN POCKET TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C DAILY CHK J DYER APVD -	09DEC2008 09DEC2008	TE Connectivity	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	ASSEMBLY, IDC SSL CONNECTOR, SMT, PASS THRU	
mm	0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±	108-2404	SIZE		
MATERIAL	FINISH	APPLICATION SPEC	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	114-13266	A200779	C-2106431	-
material_2	finish_spec_2	Customer Drawing	SCALE	SHEET	REV
			8:1	1 OF 3	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2106431-3](#)