





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD




2 POSITION
SHOWN AS SHIPPED



FOR 2, 3 AND
4 POSITIONS



FOR 1 POSITION
ONLY



- | | | |
|---|--|--|
| △ | MATERIALS AND FINISH: | |
| | - HOUSING: LCP, COLOR: NATURAL | |
| | - CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni | |

2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)


3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.
- | | | | | |
|--------|-----|------------|----|------|
| 18 AWG | MAX | INSULATION | OD | 2.20 |
| 20 AWG | MAX | INSULATION | OD | 1.90 |
| 22 AWG | MAX | INSULATION | OD | 1.70 |
| 24 AWG | MAX | INSULATION | OD | 1.45 |

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

5 WIRE SIZE MARKING IN APPROXIMATE LOCAITON SHOWN.

 COLOR CODE MARKING, STRAIGHT LINE.

7 ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




2 POSITION
SHOWN CLOSED
SCALE 8:1


RED	17.70	24 AWG	4	3-2106751-4
	13.70	24 AWG	3	3-2106751-3
	9.70	24 AWG	2	3-2106751-2
	5.70	24 AWG	1	 3-2106751-1
GREEN	17.70	22 AWG	4	2-2106751-4
	13.70	22 AWG	3	2-2106751-3
	9.70	22 AWG	2	2-2106751-2
	5.70	22 AWG	1	 2-2106751-1
BLUE	17.70	20 AWG	4	1-2106751-4
	13.70	20 AWG	3	1-2106751-3
	9.70	20 AWG	2	1-2106751-2
	5.70	20 AWG	1	 1-2106751-1
YELLOW	17.70	18 AWG	4	2106751-4
	13.70	18 AWG	3	2106751-3
	9.70	18 AWG	2	2106751-2
	5.70	18 AWG	1	 2106751-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCOY CHK 26AUG2009 O. OSAGIE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.5 1 PLC ±0.13 2 PLC ±.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU	
		PRODUCT SPEC 108-2404		SIZE CAGE CODE DRAWING NO RESTRICTED TO A200779 C-2106751 -	
MATERIAL  -  -		APPLICATION SPEC 114-13266		WEIGHT -	
		Customer Drawing		SCALE 8.1	SHEET 1 OF 3 REV C


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




1 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1





2 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCYOC	TE Connectivity			
DIMENSIONS: mm		CHK 26AUG2009 O. OSAGIE				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME			
0 PLC ±		PRODUCT SPEC	ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU			
1 PLC ±0.5		108-2404				
2 PLC ±0.13		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO			
3 PLC ±		114-13266	A200779C-2106751			
4 PLC ±		WEIGHT -				
MATERIAL -		Customer Drawing	RESTRICTED TO			
finish_spec_2		SCALE 8:1	SHEET 1 OF 3			
			REV C			



SECTION Y-Y

2106751-2 SHOWN IN POCKET TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN26AUG2009

CHKWM VAN SCYOC

26AUG2009

APVDQ OSAGIE

PRODUCT SPEC

108-2404

APPLICATION SPEC

114-13266

WEIGHT

-

Customer Drawing

SCALE8:1

SHEET1

OF3

REV

C

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.5

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

-

MATERIAL

-

material_2

TE Connectivity

NAME

ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2106751

-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2106751-2](#)