

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	PRODUCTION ISSUE	28JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H		J			P	R	S	T	U	JO	HW	JW
	Min a	Max b	Min -3,-4,-25 a	Min -12,-100 a	Max b	±10% b	Ref b	Ref b	Ref b	±10% b	±10% b	±20% b	±20% b
222D921	19.3 [.76]	13.0 [.51]	6.3 [.25]	4.5 [.18]	2.1 [.08]	44.5 [1.75]	16.3 [.64]	3.05 [.12]	1.02 [.04]	5.6 [.22]	21.8 [.86]	1.52 [.06]	1.14 [.045]
222D932	26.1 [1.03]	19.1 [.75]	7.6 [.30]	5.6 [.22]	2.6 [.10]	67.3 [2.65]	18.0 [.71]	3.05 [.12]	1.02 [.04]	8.4 [.33]	29.2 [1.15]	1.78 [.07]	1.14 [.045]
222D953	34.2 [1.35]	26.0 [1.02]	9.6 [.38]	6.6 [.26]	3.0 [.12]	81.3 [3.20]	18.8 [.74]	3.05 [.12]	1.02 [.04]	11.4 [.45]	36.3 [1.39]	1.78 [.07]	1.14 [.045]
222D963	43.6 [1.72]	34.1 [1.34]	11.4 [.45]	7.8 [.31]	3.6 [.14]	115.6 [4.55]	21.3 [.84]	3.05 [.12]	1.65 [.065]	15.5 [.61]	47.0 [1.85]	1.78 [.07]	1.14 [.045]

DIMENSIONS:

mm [INCHES]

DWN

PRAVEEN N T

28JAN2019

CHK

N NAGAR

28JAN2019

APVD

M TAYLOR

28JAN2019

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

MATERIAL

SEE SHEET 2

FINISH

—



TE Connectivity Ltd.

NAME

BOOT, 90 DEGREE,
WITH LIP

SIZE

A4

CAGE CODE

00779

DRAWING NO



222D921-XX-0THRU963-XX-0

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2


REV J

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.

0 PLC ± —
 1 PLC ± —
 2 PLC ± —
 3 PLC ± —
 4 PLC ± —
 ANGLES ± —



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-flexible ZEROHAL	RW-2082	/86;/180	S1048;S1030

ORDERING INFORMATION

222D9XX-XX-XX/XX-0

Base part number

Material dash number
(See Compatability Chart)

Modification number

Adhesive slash number
(If necessary, see Compatability Chart)

Color designator

NOTES

1. Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.

THIS DRAWING IS UNPUBLISHED.
ALL RIGHTS RESERVED.
© COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:		DWN	28JAN2019	MATERIAL	—		FINISH	—	
mm [INCHES]		PRAVEEN N T		TE Connectivity Ltd.					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	28JAN2019						
		N NAGAR							
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD	28JAN2019	NAME BOOT, 90 DEGREE, WITH LIP					
		M TAYLOR							
		PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO					
		—							
APPLICATION SPEC		WEIGHT							
—								CUSTOMER DRAWINGSCALE DNSSHEET 2 OF 2REV J	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222D932-3/86-0](#)