





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECR-12-003555	19APR2012	RS	DD
			A2	REVISED PER ECR-12-016877	20OCT2012	RS	DD
			B	REVISED PER ECR-15-004054	28JUL2015	RS	DD
			C	REVISED PER ECR-15-017995	18DEC2015	RS	DD



2 POSITION
SHOWN AS SHIPPED



FOR 2, 3 AND
4 POSITIONS



FOR 1 POSITION
ONLY


1. MATERIALS AND FINISH:
- HOUSING: LCP, COLOR: NATURAL
- CONTACTS: COPPER ALLOY, FINISH: Sn OVER Ni
2. COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. 18-24AWG SOLID OR STRANDED WIRE.
PLEASE REFER TO APPLICATION SPEC 114-13266
FOR RECOMMENDED STRAND COUNT.
- | | |
|--------------------------|------|
| 18 AWG MAX INSULATION OD | 2.20 |
| 20 AWG MAX INSULATION OD | 1.90 |
| 22 AWG MAX INSULATION OD | 1.70 |
| 24 AWG MAX INSULATION OD | 1.45 |

4. PACKAGE IN TAPE AND REEL PER EIA-481 SPECIFICATION

 WIRE SIZE MARKING IN APPROXIMATE LOCATION SHOWN.

△ COLOR CODE MARKING, STRAIGHT LINE.

△ ONE POSITION ASSEMBLY DOES NOT COMPLY WITH EIA 481 SPECIFICATION.




2 POSITION
SHOWN CLOSED
SCALE 8:1


RED	17.70	24 AWG	4	3-2106751-4
	13.70	24 AWG	3	3-2106751-3
	9.70	24 AWG	2	3-2106751-2
	5.70	24 AWG	1	 3-2106751-1
GREEN	17.70	22 AWG	4	2-2106751-4
	13.70	22 AWG	3	2-2106751-3
	9.70	22 AWG	2	2-2106751-2
	5.70	22 AWG	1	 2-2106751-1
BLUE	17.70	20 AWG	4	1-2106751-4
	13.70	20 AWG	3	1-2106751-3
	9.70	20 AWG	2	1-2106751-2
	5.70	20 AWG	1	 1-2106751-1
YELLOW	17.70	18 AWG	4	2106751-4
	13.70	18 AWG	3	2106751-3
	9.70	18 AWG	2	2106751-2
	5.70	18 AWG	1	 2106751-1
COLOR CODE	DIM D	WIRE SIZE	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26AUG2009 WM VAN SCOY CHR 26AUG2009 O. OSAGIE		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME ASSEMBLY, IDC SSL CONNECTOR, THROUGH HOLE, PASS THRU	
		PRODUCT SPEC 108-2404 APPLICATION SPEC 114-13266		SIZE A2	
MATERIAL  -  -		WEIGHT -		CAGE CODE 00779	
		Customer Drawing		DRAWING NO C-2106751	
				RESTRICTED TO -	
				SCALE 8:1 SHEET 1 OF 3 REV C	


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
			-	SEE SHEET 1	-	-




1 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



3 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



2 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1



4 POSITION
RECOMMENDED
PCB LAYOUT
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 26AUG2009
CHK WM VAN SCYOC
26AUG2009
APVD -
PRODUCT SPEC
108-2404
APPLICATION SPEC
114-13266
WEIGHT -
Customer Drawing



TE Connectivity

ASSEMBLY,
IDC SSL CONNECTOR,
THROUGH HOLE, PASS THRU

SIZE CAGE CODE DRAWING NO
A200779C-2106751

RESTRICTED TO
-

SCALE 8:1 SHEET 1 OF 3 REV C



SECTION Y-Y

2106751-2 SHOWN IN POCKET TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN26AUG2009

CHKWM VAN SCYOC

26AUG2009

APVDQ. OSAGIE

PRODUCT SPEC

108-2404

APPLICATION SPEC

114-13266

WEIGHT

-

Customer Drawing

SCALE8:1

SHEET1

OF3

REV

C

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.5

2 PLC ±0.13

3 PLC ±

4 PLC ±

ANGLES ±

FINISH

-

MATERIAL

-

material_2

TE Connectivity

NAME

ASSEMBLY,
IDC SSL CONNECTOR,
THROUGH HOLE, PASS THRU

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-2106751

RESTRICTED TO

-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2106751-1](#)