










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECO-21-006709	18JUN2021	RK	AS

SINGLE POLE SWITCH WITH DUAL COLOR LED's




PANEL CUTOUT
MAX.PANEL THICKNESS: 10.00[.394]



SPECIFICATION:
CONTACT RATING: SILVER; 3A @ 250VAC RESISTIVE
GOLD; 0.4A @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50mΩ MAX @ 1A 12VDC (INITIAL VALUE), SOLDER TERMINALS
100mΩ MAX @ 1A 12VDC (INITIAL VALUES), FLYING LEADS.
ELECTRICAL LIFE CYCLES: 50,000 MAKE AND BREAK CYCLES AT FULL LOAD.
ACTUATION FORCE: SP: 2.5±1 N, DP: 3.5±1 N
ACTUATION TRAVEL: APPROXIMATELY 3.2mm
SEALED PER IP67, IK10
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFECYCLES: MOMENTARY; 1,000,000 CYCLES
LOCKING; 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m.

MATERIALS
BUSHING: STAINLESS STEEL,
BASE: PBT (UL 94-V0), PC (UL 94-V2),
ACTUATOR: STAINLESS STEEL, PC
O-RING: SILICONE,
TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED,
HEX NUT: BRASS BASE, NICKEL PLATED,
WIRE:UL3385.
INNER ASSEMBLY: POM/PA66
SPRING: SPRING STEEL
SEALING: SILICONE



1. ALL MATERIAL AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003(ROHS).




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHIVAKUMAR S S 15FEB2017	TE Connectivity			
		CHK SANJAY SHINDIKAR 15FEB2017				
DIMENSIONS: mm [INCHES]		APVD SANJAY SHINDIKAR 15FEB2017	NAME ANTI-VANDAL SWITCH 19mm SOLDER TERMINAL FLYING LEADS, POWER LOGO DUAL COLOR LED			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C-2316366	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 5	REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-






DOUBLE POLE SWITCH WITH DUAL COLOR LED's






PANEL CUTOUT
MAX.PANEL THICKNESS: 10.00[.394]



ASSEMBLED VIEW




EXPLODED VIEW




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15FEB2017 SHIVAKUMAR S S	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK 15FEB2017 SANJAY SHINDIKAR			
		APVD 15FEB2017 SANJAY SHINDIKAR	NAME ANTI-VANDAL SWITCH 19mm SOLDER TERMINAL FLYING LEADS, POWER LOGO DUAL COLOR LED		
		PRODUCT SPEC	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-		
0 PLC ± -		WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C-2316366
1 PLC ± 0.4[.016]		CUSTOMER DRAWING			
2 PLC ± 0.25[.010]		SCALE 1:1			
3 PLC ± -		SHEET 2 of 5			
4 PLC ± -		REV A1			
ANGLES ± 2°					
FINISH -					

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



DOUBLE POLE SWITCH WITH DUAL COLOR LED's AND FLYING LEADS



WIRE=18AWG, 300V(BLACK/YELLOW/GREEN/RED/PURPLE)



ASSEMBLED VIEW



2316366

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2316366-3](#)