





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
H	-		V2	REFERENCE FOR OVERALL PITCH DIMENSION CORRECTED	09MAR2017	SS PS

PART NUMBER BOX PACKAGING	PART NUMBER REEL PACKAGING	NO OF POS "n"	DIMENSION "A" MAX
7-215083-4	215083-4	4	8,6
7-215083-6	215083-6	6	11,1
7-215083-8	215083-8	8	13,6
8-215083-0	1-215083-0	10	16,2
8-215083-2	1-215083-2	12	18,7
8-215083-4	1-215083-4	14	21,3
8-215083-6	1-215083-6	16	23,8
8-215083-8	1-215083-8	18	26,3
9-215083-0	2-215083-0	20	28,9
9-215083-4	2-215083-4	24	34,0




NOTES;

1. SHOWN IS A 10 POSITION CONNECTOR

2 FOR FLAT RIBBON CABLE REQUIREMENTS.
SEE APPLICATION SPEC 114-19016.

3 CONNECTOR-HEIGHT AFTER CABLE TERMINATION 5.1 mm AVERAGE.
DEPENDING ON PROCESSING, SEE APPLICATION SPEC 114-19016.

--	GLASS FILLED POLYESTER (RED)	HOUSING	3
TIN OVER NICKEL PLATING	PHOSPHOR BRONZE	MALE CONTACT	2
--	GLASS FILLED POLYESTER (RED)	COVER	1
FINISH	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.V.Tongerren	-	 TE Connectivity	
DIMENSIONS: mm		CHK H SPELDE	24-08-01		
		APVD H SPELDE	24-08-01		
		PRODUCT SPEC	108-19052		
MATERIAL SEE TABLE		APPLICATION SPEC	114-19016	NAME Micro-MaTch MALE-ON-WIRE CONNECTOR	
		WEIGHT	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		Customer Drawing		SIZE A3	CAGE CODE 00779
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±		SCALE 5:1		DRAWING NO C-215083	RESTRICTED TO -
		SHEET 1 OF 1		REV V2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[215083-4](#)