










REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-17-011951	16JUN2021	RK	AS



SPECIFICATION:

CONTACT RATING: SILVER; 3A @ 250VAC RESISTIVE
GOLD; 0.4A @ 20VDC OR PEAK AC
INSULATION RESISTANCE: 1,000MΩ MIN AT 500VDC
DIELECTRIC STRENGTH: 2,000V RMS @ SEA LEVEL
CONTACT RESISTANCE: 50mΩ MAX @ 1A 12VDC (INITIAL VALUE),
SOLDER TERMINALS
100mΩ MAX @ 1A 12VDC (INITIAL VALUES),
FLYING LEADS.

ELECTRICAL LIFE CYCLES: 50,000 MAKE AND BREAK CYCLES
AT FULL LOAD.

ACTUATION FORCE: SP: 2.5 ± 1 N, DP: 3.5 ± 1 N
ACTUATION TRAVEL: APPROXIMATELY 3.2mm


SEALING: IP67, IK08 (STAINLESS)
OPERATING TEMPERATURE: -20°C TO +55°C
MECHANICAL LIFECYCLES: MOMENTARY: 1,000,000 CYCLES
LOCKING: 500,000 CYCLES
HARDWARE TORQUE: 5-14 N-m.

MATERIALS

BUSHING: STAINLESS STEEL,
BASE: PBT (UL 94-V0), PC (UL 94-V2),
ACTUATOR: STAINLESS STEEL, PC
O-RING: SILICONE,
TERMINAL/CONTACT: COPPER BASE, SILVER/GOLD PLATED,
HEX NUT: BRASS BASE, NICKEL PLATED.

1. ALL MATERIAL AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003(ROHS).

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SHIVAKUMAR S S 15MAR2017 CHK SANJAY SHINDIKAR 15MAR2017		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.4[.016] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		NAME ANTI-VANDAL SWITCH 25mm, SOLDER TERMINALS MOVING RING LED PLUS POWER LOGO	
		APVD SANJAY SHINDIKAR 15MAR2017 PRODUCT SPEC - APPLICATION SPEC -		SIZE A2	
MATERIAL -		FINISH -		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-2317658	
CUSTOMER DRAWING				SCALE 1:1	
				SHEET 1 of 3	
				REV A1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2317658-4](#)