




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-20-002055	14FEB2020	AP	GF
C		REVISED PER ECO-21-005292	01MAY2021	KK	AK

△ LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -4): -1 SHOWN.

STE 2334985-1 X

0.5M - 32AWG

PPPPPLYWWSSS

00000000000000000000

TE LOGO, TE P/N, X= MFG LOCATION

LENGTH - CABLE GAGE

PN, MANUFACTURING LOCATION AND DATE CODE SERIAL NUMBER

BAR CODE

- SEE SHEET 2 FOR WIRING SCHEMATIC.
- ALL MATERIALS, COMPONENTS AND PROCESS SHALL COMPLY WITH TEC-138-702. (CONTAINS NO BANNED OR RESTRICTED SUBSTANCES).
- CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
- NO REACH SvHC SHALL BE CONTAINED ABOVE THE THRESHOLD AS DEFINED IN REACH SvHC COMPLIANCE DEFINITION IN ANNEX A OF TEC-138-702

△ TEST IN ACCORDANCE WITH IEEE802.3by.

△ LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -43): -41 SHOWN

STE 4-2334985-1 X

0.5M - 32AWG

PPPPPLYWWSSS

00000000000000000000

TE LOGO, TE P/N, X= MFG LOCATION


LENGTH - CABLE GAGE

PN, MANUFACTURING LOCATION AND DATE CODE SERIAL NUMBER


BAR CODE

△ DASH NUMBER 41 THRU 43 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

△8	32 AWG	1500 +50/-0	4-2334985-3
	32 AWG	1000 +50/-0	4-2334985-2
	32 AWG	500 +50/-0	4-2334985-1
△6	32 AWG	2000 +80/-0	2334985-4
	32 AWG	1500 +50/-0	2334985-3
	32 AWG	1000 +50/-0	2334985-2
	32 AWG	500 +50/-0	2334985-1
STANDARD	WIRE GAGE	L	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M_Y1 03MAY2018	 TE Connectivity	
DIMENSIONS:		CHK G.FRANKLIN 03MAY2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPR G.FRANKLIN 03MAY2018	NAME	
		PRODUCT SPEC -	CABLE ASSEMBLY,SFP+ TO SFP+, 28G 32 AWG	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±	APPLICATION SPEC -	SIZE	
		RESTRICTED TO		
MATERIAL	-	WEIGHT	A100779C2334985	
-	-	CUSTOMER DRAWING	SCALE 2:1 SHEET 1 OF 2 REV C	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M_Y1	03MAY2018		 TE Connectivity	
		CHK G.FRANKLIN	03MAY2018			
DIMENSIONS:		APVD G.FRANKLIN		03MAY2018		NAME CABLE ASSEMBLY, SFP+ TO SFP+, 28G 32 AWG
mm		PRODUCT SPEC				
		APPLICATION SPEC				SIZE A1
		WEIGHT				
MATERIAL		CUSTOMER DRAWING				RESTRICTED TO
						SCALE 2:1
						SHEET 2
						OF 2
						REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2334985-1](#)