


IAL : 0.25 THICK NICKEL SILVER.
ERIAL: COPPER ALLOY
MATERIAL: ALUMINUM
IAL: STAINLESS STEEL
: PLATED FILLED SILICONE




9. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.

DOCUMENT	DWN JASON YANG	01APR2014	 TE Connectivity			
UNLESS SPECIFIED	CHKD SEAN HAN	30DEC2015	NAME			
	APVD		CAGE ASSEMBLY, QSFP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK			
25	PRODUCT SPEC		SIZE			
25	108-19428		CAGE CODE			
20	APPLICATION SPEC		DRAWING NO			
+	114-32023		RESTRICTED TO			
	WEIGHT	-	A1			
			00779			
	CUSTOMER DRAWING		C-2170753			
			SCALE			
			4:1			
			SHEET			
			1 of 5			
			REV			
			A			


		TE Connectivity	
NAME			
CAGE ASSEMBLY, QSFP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	©=2170753	-
SCALE		4:1	SHEET 1 OF 5
			REV A

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION			DATE	DWN	APVD
		- SEE SHEET 1			-	-	-


HEAT SINK OPTIONS



PCI HEAT SINK
SCALE 3:1




SAN HEAT SINK
SCALE 3:1




NETWORKING HEAT SINK
SCALE 3:1


OF REAR LEGS OPTIONS



2 REAR LEGS
SCALE 5:1







1 REAR LEG
SCALE 5:1



0 REAR LEG
SCALE 5:1





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity
		CHK: SEAN HAN 30DEC2015	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ± FINISH	NAME
			CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK
MATERIAL	-	PRODUCT SPEC	SIZE
-	-	108-19428	CAGE CODE
-	-	APPLICATION SPEC	DRAWING NO
		114-32023	A100779C=2170753
		WEIGHT	RESTRICTED TO
		Customer Drawing	-
		SCALE 4:1	SHEET 2 OF 5
			REV A

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity
		CHK: SEAN HAN 30DEC2015	
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK
mm		PRODUCT SPEC: 108-19428	
		APPLICATION SPEC: 114-32023	SIZE: A100779C=2170753
		WEIGHT: -	
MATERIAL: -		Customer Drawing	RESTRICTED TO: -
		SCALE: 4:1	SHEET 3 OF 5
		REV: A	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	TE Connectivity	
DIMENSIONS:		CHK SEAN HAN 30DEC2015		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME	CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK
	0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.25 3 PLC ± 0.100 4 PLC $\pm$ ANGLES $\pm$ FINISH	PRODUCT SPEC 108-19428	SIZE	100779
MATERIAL		APPLICATION SPEC 114-32023	CAGE CODE	2170753
		WEIGHT	DRAWING NO	Customer Drawing
			SCALE	4:1
			SHEET	4
			OF	5
			REV	A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170753-7](#)