







2170753-2 AS SHOWN

- | | | | |
|-------|-------------|-------------|----------------|
| 23.0 | 1 | NETWORKING | 2170753-9 |
| 16.0 | 1 | SAN | 2170753-8 |
| 13.7 | 1 | PCI | 2170753-7 |
| 23.0 | 0 | NETWORKING | 2170753-6 |
| 16.0 | 0 | SAN | 2170753-5 |
| 13.7 | 0 | PCI | 2170753-4 |
| 23.0 | 2 | NETWORKING | 2170753-3 |
| 16.0 | 2 | SAN | 2170753-2 |
| 13.7 | 2 | PCI | 2170753-1 |
| DIM A | # REAR PINS | APPLICATION | PART
NUMBER |


4805 (3/11)

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION			DATE	DWN	APVD
		SEE SHEET 1			-	-	-


HEAT SINK OPTIONS



PCI HEAT SINK
SCALE 3:1




SAN HEAT SINK
SCALE 3:1




NETWORKING HEAT SINK
SCALE 3:1


OF REAR LEGS OPTIONS



2 REAR LEGS
SCALE 5:1







1 REAR LEG
SCALE 5:1



0 REAR LEG
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	 TE Connectivity	
		CHK SEAN HAN 30DEC2015		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ± FINISH	NAME CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	RESTRICTED TO -
		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT -	SIZE A100779C=2170753	
MATERIAL - -		Customer Drawing	SCALE 4:1	SHEET 2 OF 5
				REV A

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014	TE Connectivity
		CHK: SEAN HAN 30DEC2015	
DIMENSIONS:		APVD: -	NAME: CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK
mm		PRODUCT SPEC: 108-19428	
		APPLICATION SPEC: 114-32023	SIZE: A100779C=2170753
		WEIGHT: -	
MATERIAL: -		Customer Drawing	RESTRICTED TO: -
		SCALE: 4:1	SHEET: 3 OF 5
		REV: A	




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

D

C


B

A




RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 1 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1

RECOMMENDED PCB LAYOUT
SINGLE TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ±0.05
SCALE 6:1



DETAIL B
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 01APR2014 CHK: SEAN HAN 30DEC2015 APVD: -	NAME: CAGE ASSEMBLY, QSFP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	SIZE	RESTRICTED TO
mm	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES FINISH	108-19428 APPLICATION SPEC	114-32023	-
MATERIAL	-	WEIGHT	Customer Drawing	-
-	-	-	-	-
SCALE 4:1			SHEET 4 OF 5	REV A



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2170753-6](#)