

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	24 JAN2022	SCB	PS

2385008-3 AS SHOWN

NOTES:

1 MATERIALS & FINISH
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN
CONTACT : BRASS, TIN PLATED

3. ELECTRICAL
RATED CURRENT AND VOLTAGE : 16AMP 300V(UG B)
: 10AMP 300V(UG D)
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

4 TOLERANCE NOT CUMULATIVE

82.88	16	1-2385008-6
77.80	15	1-2385008-5
72.72	14	1-2385008-4
67.64	13	1-2385008-3
62.56	12	1-2385008-2
57.48	11	1-2385008-1
52.40	10	1-2385008-0
47.32	9	2385008-9
42.24	8	2385008-8
37.16	7	2385008-7
32.08	6	2385008-6
27.00	5	2385008-5
21.92	4	2385008-4
16.84	3	2385008-3
11.76	2	2385008-2
DIM A	NO. OF POS.	TE PN



NAME
TERMINAL BLOCK, 90 DEG HEADER,
PITCH 5.08mm, TAIL LENGTH 4.5mm

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2385008	-

DWN	24 JAN2022
CHK	SHRICHARANA B
APVD	24 JAN2022
PRASHANTH S	
PRODUCT SPEC	108-32299
APPLICATION SPEC	114-32242
WEIGHT	-

CUSTOMER DRAWING	SCALE	4:1	SHEET	1 OF 1	REV	A
------------------	-------	-----	-------	--------	-----	---

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL	FINISH
1	1

HEADER FOOTPRINT

RECOMMENDED PCB LAYOUT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2385008-4](#)