






2198226
FINISHED ASSEMBLY
SCALE 4:1

- △ MATERIAL:
CAGE ASSEMBLY: 0.25mm THICK NICKEL SILVER ALLOY
GASKET RETENTION PLATE: STAINLESS STEEL
EMI GASKET: PLATED FILLED SILICONE
HEATSINK/LIGHTPIPE CLIP: STAINLESS STEEL
HEATSINK: ALUMINUM
LIGHTPIPE: POLYCARBONATE, CLEAR
- △ FINISH:
HEATSINK: ELECTROLESS NICKEL
HEATSINK/LIGHTPIPE CLIP: PASSIVATE
- △ DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ PADS AND VIAS CHASSIS GROUND.
5. MATES WITH SFP MSA COMPLIANT RECIEVERS.
6. INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OR ASME Y14.5M-1994.
- △ HOLE PATTERN REPEATS FOR EACH PORT, SPACING BETWEEN PORTS IS 14.25mm.
- △ REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- △ REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.


- △ MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.5mm
11. CERTAIN MATING TRANCEIVERS MAY REQUIRE ADDITIONAL PCB THICKNESS THAT WOULD NEED TO BE DETERMINED BY THE CUSTOMER.
12. PRODUCT COMPLIES WITH SPECIFICATION SFF-8433 IMPROVED PLUGGABLE FORM FACTOR FOR SFP+ GANGED CAGES.
- △ DIMENSION APPLIES PRIOR TO INSERTION OF SFP MODULE.
- △ HEATSINK, HEATSINK CLIP, AND LIGHTPIPE SHIPPED UNASSEMBLED TO CAGE ASSEMBLY. CAGE ASSEMBLY TO BE PRESSED INTO PCB PRIOR TO ATTACHING HEATSINK, HEATSINK CLIP, AND LIGHTPIPE TO THE CAGE ASSEMBLY.
- △ PACKAGED AS A COMPLETE ASSEMBLY.




△3	22.5	NETWORKING, TALL	2198226-4
△3	18.1	NETWORKING, SHORT	2198226-3
△4	15.5	SAN	2198226-2
△4	13.2	PCI	2198226-1
	A MAX	APPLICATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. MATTHEWS CHK M. SCHMITT APVD M. SCHMITT	14OCT2011 14OCT2011 14OCT2011	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.13 1 PLC ±0.1 2 PLC ±0.08 3 PLC ±.05 4 PLC ±.05 ANGLES ±.1		SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI GASKET WITH HEATSINK AND LIGHTPIPE	
MATERIAL		FINISH		SIZE	
				CAGE CODE DRAWING NO	
				RESTRICTED TO	
				A100779C=2198226	
				SCALE 5:1 SHEET 1 OF 3 REV A	
				CUSTOMER DRAWING	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00	-	-	SEE SHEET 1	-	-	-



RECOMMENDED BEZEL CUTOUT
SCALE 4:1




2198226
MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL



2198226
MOUNTED ON PCB
SHOWN THRU RECOMMENDED BEZEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MATTHEWS CHK M. SCHMITT APVD M. SCHMITT	14OCT2011 14OCT2011 14OCT2011	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.13 1 PLC ±0.1 2 PLC ±0.08 3 PLC ±0.05 4 PLC ±0.05		SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI GASKET WITH HEATSINK AND LIGHTPIPE	
MATERIAL		FINISH		RESTRICTED TO	
CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 3	



CROSS-HATCHED AREA
DENOTES EXPOSED
CHASSIS GROUND

1.1

2X 2

2X 12.05

Technical drawing showing two holes in a part. The left hole has a diameter of $4 \times 3.56 \pm 0.1$ mm and a depth of 0.1 mm. The right hole has a diameter of $4 \times 2.54 \pm 0.1$ mm. The distance between the centers of the two holes is 6.5 mm. The drawing includes a feature control frame for the left hole with a circular symbol and the letters 'A' and 'B'.

DETAIL E
SCALE 10:1

CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2198226-4](#)