





REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	PN 2-282815-6 ADDED	26MAR2018	RK	PS
	C4	PART STATUS UPDATED	05JUL2021	SB	SS



282815-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT



OBSOLETE	ORANGE	15.24	3	2-282815-6
	GREEN	127.00	25	2-282815-5
	GREEN	121.92	24	2-282815-4
	GREEN	116.84	23	2-282815-3
	GREEN	111.76	22	2-282815-2
	GREEN	106.68	21	2-282815-1
	GREEN	101.60	20	2-282815-0
	GREEN	96.52	19	1-282815-9
	GREEN	91.44	18	1-282815-8
	GREEN	86.36	17	1-282815-7
	GREEN	81.28	16	1-282815-6
	GREEN	76.20	15	1-282815-5
	GREEN	71.12	14	1-282815-4
	GREEN	66.04	13	1-282815-3
	GREEN	60.96	12	1-282815-2
	GREEN	55.88	11	1-282815-1
	GREEN	50.80	10	1-282815-0
	GREEN	45.72	9	282815-9
	GREEN	40.64	8	282815-8
	GREEN	35.56	7	282815-7
	GREEN	30.48	6	282815-6
	GREEN	25.40	5	282815-5
	GREEN	20.32	4	282815-4
	GREEN	15.24	3	282815-3
	GREEN	10.16	2	282815-2

COLOR	DIM. A	NO OF POS.	PART NUMBER
NAME TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE OPEN ENDS, STACKING 5.08mm PITCH			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282815	
SCALE 3:1		SHEET 1 OF 2	REV C4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 25JUL2001
DIMENSIONS: mm		CHK D. BIEVENOUR 25JUL2001
	0 PLC	±
	1 PLC	±0.3
	2 PLC	±0.25
	3 PLC	±
	4 PLC	±
ANGLES		±2
FINISH		±
MATERIAL SEE NOTES		PRODUCT SPEC 108-20166
		APPLICATION SPEC 114-20079
		WEIGHT -
		CUSTOMER DRAWING


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:

1. MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0.
TERMINAL: BRASS, TIN PLATED.
2. MECHANICAL
MAX. INSERTION FORCE PER POLE : 3.0 N
MIN. WITHDRAWAL FORCE PER POLE : 1.5 N
MIN. PC BOARD HOLES DIAMETER : 1.4 mm
MAX. PC BOARD THICKNESS : 2.4 mm
3. ELECTRICAL
WIRE RANGE : 12-30 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 15 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)
4. END-TO-END STACKABLE WITHOUT LOSS OF
CENTERLINE SPACING.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE NO E60677.
6. OPERATING TEMPERATURE RANGE: -40°C TO +110°C

 NOT CUMULATIVE TOLERANCE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 25JUL2001	 TE Connectivity				
		CHK D. BIEVENOUR 25JUL2001					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 25JUL2001	NAME TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE OPEN ENDS, STACKING 5.08mm PITCH			
	0 PLC ±° 1 PLC ±.2 2 PLC ±.25 3 PLC ±° 4 PLC ±° ANGLES ±2		PRODUCT SPEC 108-20166	SIZE A300779 CAGE CODE C-282815 DRAWING NO RESTRICTED TO			
			APPLICATION SPEC 114-20079				
	MATERIAL SEE NOTES	FINISH SEE NOTES		WEIGHT -			
CUSTOMER DRAWING			SCALE 3:1		SHEET 2 OF 2		REV C4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[282815-8](#)