





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N2	REVISED PER ECN-22-156403	03JUN2022	RK	CSD

 WIRE RANGE	 E13288 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED IR: STRANDED	16-14 AWG STRANDED	WIRE SIZE PER TABLE SOLID OR STRANDED IR: STRANDED

-  STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
-  WIRE INSULATION DIA: SEE TABLE.
-  BODY MATERIAL THK: 0.787[.031]±0.051[.002].
-  BODY: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
-  SLEEVE: TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545.
-  BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
-  APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
-  MEETS MS25036-110, CLASS 1.
-  MEETS M7928/1-45, CLASS 1.
-  MEETS M7928/1-54, CLASS 1.
-  UL LISTED
-  CSA CERTIFIED



STYLE A



STYLE B
INSULATION RESTRICTING

 	100	LOOSE PIECE, BOX	16-14*	2.667[.105]-3.810[.150]	16-14	--	A	 	  	8-320564-1
 	500	320564 ON TAPE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A			2-320564-3
	500	LOOSE PIECE	14*	1.981[.078]-3.302[.130]	14	GREEN	B	 	  	2-320564-2
	500	LOOSE PIECE	16*	1.600[.063]-3.302[.130]	16	BLUE	B			2-320564-1
 	500	LOOSE PIECE	16-14*	2.667[.105]-3.810[.150]	16-14	--	A	 	  	320564
QTY		PACKAGE TYPE	 STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY FINISH	SLEEVE FINISH	PART NO

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH CHK T MICHELUTTI APVD T MICHELUTTI PRODUCT SPEC UL 486 A-B ¹¹ APPLICATION SPEC 114-2157 WEIGHT -		13JAN10 13JAN10 13JAN10		 TE Connectivity						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX		DIMENSIONS: mm[INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127(.005) 4 PLC ± - ANGLES ± -		NAME TERMINAL, RING TONGUE, PIDG, WIRE SIZE: 16-14 AWG PIDG IR 16 & 14 AWG							
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm²[2,050-5,180] STRANDED OR SOLID													
TOOLING INFORMATION		1-800-722-1111				MATERIAL 		FINISH INSULATION COLOR-BLUE		SIZE A2		CAGE CODE 00779		DRAWING NO C-320564		RESTRICTED TO -	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						CUSTOMER DRAWING		SCALE 5:1		SHEET 1 of 1		REV N2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-320564-2](#)