

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
OY			B	REVISED PER ECR-18-002882	21FEB2018	IT	SH

⚠ MATERIAL:
CAGE ASSEMBLY:
0.25mm THICK NICKEL SILVER ALLOY
EMI SPRINGS: COPPER ALLOY
HEAT SINK: ALUMINUM
HEAT SINK CLIP: STAINLESS STEEL.

⚠ 2 FINISH:
HEAT SINK: ELECTROLESS NICKEL
HEAT SINK CLIP: PASSIVATE.
EMI SPRINGS: 0.8µm MIN MATTE TIN OVER
0.8µm MIN NICKEL, NON-PLATED EDGES PERMISSIBLE.

⚠ 3 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

⚠ 5 PADS AND VIAS CHASSIS GROUND.

5. MATES WITH SFP MSA COMPLIANT RECIEVERS.

6. INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OR ASME Y14.5M-1994.

⚠ 7 MINIMUM PC BOARD THICKNESS:
SINGLE SIDED: 1.5mm
DOUBLE SIDED: 2.25mm

⚠ 8 HOLE PATTERN REPEATS FOR EACH PORT, SPACING BETWEEN PORTS IS 14.25mm.

⚠ 9 REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.


⚠ 10 REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.

11. CERTAIN MATING TRANCEIVERS MAY REQUIRE ADDITIONAL PCB THICKNESS THAT WOULD NEED TO BE DETERMINED BY THE CUSTOMER.


12. PRODUCT COMPLIES WITH SPECIFICATION SFF-8433 IMPROVED PLUGGABLE FORM FACTOR FOR SFP+ GANGED CAGES.

⚠ 13 DIMENSION APPLIES PRIOR TO INSERTION OF SFP MODULE.


⚠ 14 WITH BELLY GASKET: RF ABSORBER





2198230-1,2,3,4
FINISHED ASSEMBLY WITH
PIN TYPE HEAT SINK



2198230-5,6,7,8
FINISHED ASSEMBLY WITH
FIN TYPE HEAT SINK




1-2198230-4
FINISHED ASSEMBLY WITH
PIN TYPE HEAT SINK, WITH BELLY GASKET



APPROXIMATE LOCATION
OF DATE CODE


FIN TYPE	22.5	NETWORKING, TALL	2198230-8
FIN TYPE	18.1	NETWORKING, SHORT	2198230-7
FIN TYPE	15.5	SAN	2198230-6
FIN TYPE	13.2	PCI	2198230-5
PIN TYPE	22.5	NETWORKING, TALL	1-2198230-4
PIN TYPE	22.5	NETWORKING, TALL	2198230-4
PIN TYPE	18.1	NETWORKING, SHORT	2198230-3
PIN TYPE	15.5	SAN	2198230-2
PIN TYPE	13.2	PCI	2198230-1
HEAT SINK	A 13 DESCRIPTION		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTINE 06OCT2011	 TE Connectivity	
DIMENSIONS:		CHK M. SCHMITT 06OCT2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. SCHMITT 06OCT2011	NAME SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI SPRINGS, HEAT SINK	
		PRODUCT SPEC 108-2364		
	FINISH	APPLICATION SPEC 114-13120	SIZE A100779	
		WEIGHT -		
MATERIAL		Customer Drawing	SCALE 2:1	
			SHEET 1 OF 4	
			REV B	




2198230-1
MOUNTED BELLY TO BELLY
SCALE 3:1


LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
					-	SEE SHEET 1	-




RECOMMENDED BEZEL CUT-OUT
SINGLE SIDED APPLICATIONS
SCALE 4:1



RECOMMENDED BEZEL CUT-OUT
BELLY TO BELLY APPLICATIONS




2198230-1
MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL






2198230-1
MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C. VALENTINE	06OCT2011	 TE Connectivity	
				CHK M. SCHMITT	06OCT2011		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. SCHMITT	06OCT2011	NAME	
mm		0 PLC ±0.13 1 PLC ±0.1 2 PLC ±0.08 3 PLC ±0.05 4 PLC ±0.05		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI SPRINGS, HEAT SINK	
		ANGLES ±1		WEIGHT -		SIZE CAGE CODE DRAWING NO	
MATERIAL		FINISH		Customer Drawing		RESTRICTED TO	
				A100779		C=2198230	
				SCALE 6:1		SHEET 2 OF 4	
						REV B	






LOC		DIST		REVISONS			
GP		00		P	LTR	DESCRIPTION	DATE
						SEE SHEET 1	





LOC		DIST		REVISONS			
GP		00		P	LTR	DESCRIPTION	DATE
						SEE SHEET 1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2198230-3](#)