


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	REVISED PER ECN-22-150900	28APR2022	RK	CSD

AMP
WIRE RANGE

22-16 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 22-18* APPROX AS SHOWN
-
- 22-16 TERMINALS ARE STAMPED 22-18 IN
-
- ACCORDANCE WITH MILITARY SPEC SAE AS7928
-
- COMMERCIAL WIRE RANGE IS 22-16

2

3

4

5

6

7

8

9

10

11

7 6	100	170°C[338°F] MAX	LOOSE PIECE, BOX	2	8-34114-1
7 6	5000	170°C[338°F] MAX	34114 ON TAPE	2	2-34114-2
7 6	1000	343°C[649°F] MAX	LOOSE PIECE	5	34114-4
7 6	1000	170°C[338°F] MAX	LOOSE PIECE	2	34114
	QTY	MAX TEMP.	PACKAGE TYPE	FINISH	PART NUMBER

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

FOR APPLICATION
TOOLING INFORMATION

FOR ORDER ENTRY

PRODUCT INFORMATION CENTER
1-800-522-6752

TOOLING ASSISTANCE CENTER
1-800-722-1111

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
SEE TABLE

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
0.26-1.65mm²[509-3260] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

9

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.127[.005]
4 PLC ± -
ANGLES ± -

FINISH
SEE TABLE

DWN
TA BRINKMAN
3-10-93

CHK
DA PATTERSON
3-10-93

APVD
DE MILLER
3-10-93

PRODUCT SPEC

11

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL, RING TONGUE,
SOLISTRAND
22-16 AWG

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-34114

RESTRICTED TO
-

SCALE
8:1

SHEET
1 OF 1

REV
D3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[34114](#)