

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	V	PRODUCTION ISSUE	30JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H		J		K		P	R	S	T	HW	JW & KW	C	Weight Nom lb/[gms]
	Min a	Max b	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±10% b	±20% b	±20% b	±5% b	
382A012	13.2 [.52]	6.1 [.24]	6.6 [.26]	3.3 [.13]	6.6 [.26]	3.3 [.13]	22.4 [.88]	19.3 [.76]	23.9 [.94]	15.5 [.61]	1.52 [.06]	1.02 [.04]	22 1/2*	1.81 [.004]
382A023	26.9 [1.06]	12.4 [.49]	13.2 [0.52]	6.1 [.24]	13.2 [.52]	6.1 [.24]	38.1 [1.50]	43.2 [1.70]	53.3 [2.10]	33.0 [1.30]	2.54 [.10]	1.52 [.06]	22 1/2*	11.79 [.026]
382A034	38.6 [1.52]	18.0 [.71]	26.9 [1.06]	12.4 [.49]	26.9 [1.06]	12.4 [.49]	65.5 [2.58]	78.7 [3.10]	78.7 [3.10]	55.9 [2.20]	3.05 [.12]	2.54 [.10]	22 1/2*	63.96 [.141]
382A046	55.6 [2.19]	25.9 [1.02]	26.9 [1.06]	12.7 [.50]	26.9 [1.06]	12.7 [.50]	85.1 [3.35]	94.0 [3.70]	111.8 [4.40]	71.1 [2.80]	4.57 [.18]	2.54 [.10]	22 1/2*	112.95 [.249]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.


COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.50[.1]
2 PLC	± 0.25[.01]
3 PLC	± 0.13[.005]
4 PLC	± -
ANGLES	± 1°



DWN 30JAN2019

PRAVEEN N T

CHK 30JAN2019

N NAGAR

APVD 30JAN2019

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

—

—

—

WEIGHT

—

MATERIAL

SEE SHEET 2

FINISH

—



TE Connectivity Ltd.

NAME

TRANSITION, Y

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C=

382A0XX-XX-0

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV V

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

## COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, semi-flexible Zerohal	RW-2082	/86;/180	S1048; S1030

## ORDERING INFORMATION

	382A0XX	-XX	-XX	/XX	-0
BASE PART NUMBER					
MATERIAL DASH NUMBER (SEE COMPATABILITY CHART)					
MODIFICATION NUMBER					
ADHESIVE SLASH NUMBER (IF NECESSARY, SEE COMPATABILITY CHART)					
COLOR DESIGNATOR					

## NOTES:

- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
  - AS SUPPLIED
  - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
- MOLDING PORTS ARE OPTIONAL. WHEN -00 MODIFICATION NUMBER IS SPECIFIED MOLDING PORTS WILL BE LOCATED AS SHOWN.
- WEIGHT SHOWN IN TABLE OF DIMENSIONS IS BASED ON POLYOLEFIN PART.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - TE Connectivity Ltd.



THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]		DWN PRAVEEN N T	30JAN2019	MATERIAL —		FINISH —	
		CHK N NAGAR	30JAN2019	<div>TE Connectivity Ltd.</div>			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M TAYLOR	30JAN2019				
		PRODUCT SPEC —		NAME TRANSITION, Y			
0 PLC ± — 1 PLC ± 0.50[.1] 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± — ANGLES ± 1°		APPLICATION SPEC —					
		WEIGHT		SIZE A4	CAGE CODE 00779	DRAWING NO C-382A0XX-XX-0	RESTRICTED TO —
CUSTOMER DRAWING				SCALE DNS	SHEET 2	OF 2	REV V

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[382A046-3-0](#) [382A034-100/86-0](#)