

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

1

2

4

3

5

Ø14.53 MAX
[.572]

33.53 MAX
[1.320]

FIGURE 1

FIGURE 2

RECOMMENDED STRIP LENGTH

1

2

3

4

5

6

7

8

9

10

CABLE USED WITHOUT SPACER

CABLE USED WITH SPACER

SEE I.S. 9021

PARTS PACKAGED UNASSEMBLED

USE AMP HAND TOOL: 220190-1

SPECIAL PACKAGING: INDIVIDUALLY PACKAGED IN PRE-PRINTED BAG WITH SPECIAL GRAPHICS

CONNECTOR INDIVIDUALLY PACKAGED

BULK PACKAGE

RG-188/U, 316/U TYPE DOUBLE BRAID AND JIS CABLES 1.5D-2V, 1.5D-XV & 1.5D-XVS

SPECIAL PACKAGING: BULK PACKAGE 25 PIECES

OBSOLETE	6	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	227423-1	9-221132-1	222246-6	413636-2	9-221128-9			
OBSOLETE	6	BELDEN 9907, 89907 & RG-141/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	1-222246-6	413636-1	9-221128-8			
OBSOLETE	6	RG-180/U, 195/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	-	-	9-413658-1	1-222246-3	413636-3	9-221128-7			
	6	RG-179/U, 187/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-0	1-222246-3	413636-3	9-221128-6			
	6	RG-174/U, 188/U, 316/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-0	1-222246-0	413636-3	9-221128-5			
OBSOLETE	6	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-5	413636-1	9-221128-4			
OBSOLETE	7	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-2	413636-4	9-221128-3			
OBSOLETE	7 7 7	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-4	413636-2	9-221128-2			
OBSOLETE	6	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-2	413636-1	9-221128-1			
OBSOLETE	6	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-2	413636-1	9-221128-0			
OBSOLETE	6	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-2	413636-1	9-221128-0			
OBSOLETE	6	BELDEN 1167A	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	-	-	9-413658-1	1-222246-0	413636-3	3-221128-4			
OBSOLETE	10	7	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-2	1-222246-0	413636-3	3-221128-2			
SUPERSEDED BY 2-221128-5	10	JIS CABLE 3D-2V	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	8-221132-9	1-222246-6	413636-6	3-221128-1			
	6	RG-180/U, 195/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	-	-	9-413658-1	1-222246-3	413636-3	3-221128-0			
OBSOLETE	-	7	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-2	1-222246-0	413636-3	2-221128-9			
	6	BELDEN 9907, 89907 & RG-141/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	1-222246-6	413636-1	2-221128-7			
OBSOLETE	6	RG-180/U, 195/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	-	-	9-413658-1	1-222246-3	413636-3	2-221128-5			
	6	RG-179/U, 187/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-0	1-222246-3	413636-3	2-221128-3			
SUPERSEDED BY 2-5221128-1	6	RG-174/U, 188/U, 316/U	4.52	[.178]	1.73	[.068]	58465-3	FIG 1	227194-1	-	9-413658-0	1-222246-0	413636-3	2-221128-1			
	6	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-5	413636-1	2-221128-0			
SUPERSEDED BY 1-221128-2	6	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-5	413636-4	1-221128-9			
	6	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	227423-1	9-221132-1	222246-6	413636-2	1-221128-8			
	6	BELDEN 9266	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-2	413636-2	1-221128-7			
OBSOLETE	-	BELDEN 9209	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-6	413636-5	1-221128-6			
SUPERSEDED BY 1-221128-2	7	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-5	413636-4	1-221128-5			
	7 7 7	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-6	413636-2	1-221128-4			
OBSOLETE	7 7 7	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-6	413636-2	1-221128-4			
OBSOLETE	7	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-5	413636-1	1-221128-3			
OBSOLETE	7	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-2	413636-4	1-221128-2			
	7 7 7	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-4	413636-2	1-221128-1			
	6	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-2	413636-1	1-221128-0			
OBSOLETE	-	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-7	413636-4	221128-9			
OBSOLETE	7 7	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-8	413636-2	221128-8			
OBSOLETE	7 7	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-8	413636-2	221128-8			
OBSOLETE	-	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-7	413636-1	221128-7			
SUPERSEDED BY 221128-3	-	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-5	413636-4	221128-6			
	7 7	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-6	413636-2	221128-5			
SUPERSEDED BY 221128-2	7 7	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-6	413636-2	221128-5			
	-	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-5	413636-1	221128-4			
SUPERSEDED BY 221128-1	-	BELDEN 8281	8.23	[.324]	1.73	[.068]	58465-2	FIG 1	-	-	9-221132-2	222246-2	413636-4	221128-3			
OBSOLETE	-	RG-62/U, 62A/U, 62B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 2	-	227423-1	9-221132-1	222246-4	413636-2	221128-2			
	-	RG-59/U, 59A/U, 59B/U	6.48	[.255]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-1	222246-4	413636-2	221128-2			
	-	RG-58/U, 58A/U, 58B/U, 58C/U	5.41	[.213]	1.73	[.068]	58465-1	FIG 1	-	-	9-221132-0	222246-2	413636-1	221128-1			
REMARKS	FOR USE WITH CABLE	FERRULE	CONTACT	DIE SET	5	STRIP LENGTH	5	TUBING QTY=1	4	SPACER QTY=1	3	FERRULE QTY=1	2	CONTACT, PLUG QTY=1	1	PLUG ASSEMBLY QTY=1	PART NUMBER
		HEX CRIMP HEIGHTS															

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.41 [016] 4 PLC ± - ANGLES ± - FINISH -

MATERIAL -

DWN M. E. COWHER 11-18-92

CHK M. PHILLIPS 1-29-93

APVD M. PHILLIPS 1-29-93

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 0.000000

CUSTOMER DRAWING

TE Connectivity

PLUG, COMMERCIAL BNC

SIZE CAGE CODE DRAWING NO RESTRICTED TO

100779C=221128

SCALE 4:1 SHEET 1 OF 1 REV AD3

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-221128-7](#)