






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
AJ	16	C		PER EC 0514-0184-04	01DEC2004	JGH



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 BERYLLIUM COPPER PER QQ-C-530.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81 μ m [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204, 0.76 μ m [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

222132-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DIN J. LIPPERT 4-13-92	tyco <i>Electronics</i>		Tyco Electronics Corporation Harriaburg, PA 17105-3608										
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A. GABANY 4-14-92	APVD A. GABANY 4-14-92		NAME JACK, VERTICAL, PCB 75 OHM, SERIES BNC —										
		0 PLC ± —		PRODUCT SPEC		SIZE A1			CAGE CODE 00779			DRAWING NO 222132			RESTRICTED TO —		
		1 PLC ± —															
		2 PLC ± 0.20 [.008]															
		3 PLC ± —															
4 PLC ± —		4 PLC ± —		APPLICATION SPEC													
ANGLES ± —		± —		WEIGHT —													
MATERIAL SEE NOTES 1-5		FINISH SEE NOTES 6-8															
CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 1		REV C							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222132-1](#)