




D

C

B

A

D

C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

	99.06	[3.900]	101.60	[4.000]	80		9-535542-0	
	96.52	[3.800]	99.06	[3.900]	78		8-535542-9	
	93.98	[3.700]	96.52	[3.800]	76		8-535542-8	
	91.44	[3.600]	93.98	[3.700]	74		8-535542-7	
	88.90	[3.500]	91.44	[3.600]	72		8-535542-6	
	86.36	[3.400]	88.90	[3.500]	70		8-535542-5	
	83.82	[3.300]	86.36	[3.400]	68		8-535542-4	
	81.28	[3.200]	83.82	[3.300]	66		8-535542-3	
	78.74	[3.100]	81.28	[3.200]	64		8-535542-2	
	76.20	[3.000]	78.74	[3.100]	62		8-535542-1	
	73.66	[2.900]	76.20	[3.000]	60		8-535542-0	
	71.12	[2.800]	73.66	[2.900]	58		7-535542-9	
	68.58	[2.700]	71.12	[2.800]	56		7-535542-8	
	66.04	[2.600]	68.58	[2.700]	54		7-535542-7	
	63.50	[2.500]	66.04	[2.600]	52		7-535542-6	
	60.96	[2.400]	63.50	[2.500]	50		7-535542-5	
	58.42	[2.300]	60.96	[2.400]	48		7-535542-4	
	55.88	[2.200]	58.42	[2.300]	46		7-535542-3	
	53.34	[2.100]	55.88	[2.200]	44		7-535542-2	
	50.80	[2.000]	53.34	[2.100]	42		7-535542-1	
	48.26	[1.900]	50.80	[2.000]	40		7-535542-0	
	45.72	[1.800]	48.26	[1.900]	38		6-535542-9	
	43.18	[1.700]	45.72	[1.800]	36		6-535542-8	
	40.64	[1.600]	43.18	[1.700]	34		6-535542-7	
	38.10	[1.500]	40.64	[1.600]	32		6-535542-6	
	35.56	[1.400]	38.10	[1.500]	30		6-535542-5	
	33.02	[1.300]	35.56	[1.400]	28		6-535542-4	
	30.48	[1.200]	33.02	[1.300]	26		6-535542-3	
	27.94	[1.100]	30.48	[1.200]	24		6-535542-2	
	25.40	[1.000]	27.94	[1.100]	22		6-535542-1	
	22.86	[.900]	25.40	[1.000]	20		6-535542-0	
	20.32	[.800]	22.86	[.900]	18		5-535542-9	
	17.78	[.700]	20.32	[.800]	16		5-535542-8	
	15.24	[.600]	17.78	[.700]	14		5-535542-7	
	12.70	[.500]	15.24	[.600]	12		5-535542-6	
		10.16	[.400]	12.70	[.500]	10		5-535542-5
		7.62	[.300]	10.16	[.400]	8		5-535542-4
		5.08	[.200]	7.62	[.300]	6		5-535542-3
		2.54	[.100]	5.08	[.200]	4		5-535542-2
		-	2.54	[.100]	2		5-535542-1	
FINISH	B	A	NO OF POSN	PART NUMBER				

		99.06[3.900]	101.60[4.000]	80		4-535542-0
		96.52[3.800]	99.06[3.900]	78		3-535542-9
		93.98[3.700]	96.52[3.800]	76		3-535542-8
		91.44[3.600]	93.98[3.700]	74		3-535542-7
		88.90[3.500]	91.44[3.600]	72		3-535542-6
		86.36[3.400]	88.90[3.500]	70		3-535542-5
		83.82[3.300]	86.36[3.400]	68		3-535542-4
		81.28[3.200]	83.82[3.300]	66		3-535542-3
		78.74[3.100]	81.28[3.200]	64		3-535542-2
		76.20[3.000]	78.74[3.100]	62		3-535542-1
		73.66[2.900]	76.20[3.000]	60		3-535542-0
		71.12[2.800]	73.66[2.900]	58		2-535542-9
		68.58[2.700]	71.12[2.800]	56		2-535542-8
		66.04[2.600]	68.58[2.700]	54		2-535542-7
		63.50[2.500]	66.04[2.600]	52		2-535542-6
		60.96[2.400]	63.50[2.500]	50		2-535542-5
		58.42[2.300]	60.96[2.400]	48		2-535542-4
		55.88[2.200]	58.42[2.300]	46		2-535542-3
		53.34[2.100]	55.88[2.200]	44		2-535542-2
		50.80[2.000]	53.34[2.100]	42		2-535542-1
		48.26[1.900]	50.80[2.000]	40		2-535542-0
		45.72[1.800]	48.26[1.900]	38		1-535542-9
		43.18[1.700]	45.72[1.800]	36		1-535542-8
		40.64[1.600]	43.18[1.700]	34		1-535542-7
		38.10[1.500]	40.64[1.600]	32		1-535542-6
		35.56[1.400]	38.10[1.500]	30		1-535542-5
		33.02[1.300]	35.56[1.400]	28		1-535542-4
		30.48[1.200]	33.02[1.300]	26		1-535542-3
		27.94[1.100]	30.48[1.200]	24		1-535542-2
		25.40[1.000]	27.94[1.100]	22		1-535542-1
		22.86[.900]	25.40[1.000]	20		1-535542-0
		20.32[.800]	22.86[.900]	18		535542-9
		17.78[.700]	20.32[.800]	16		535542-8
		15.24[.600]	17.78[.700]	14		535542-7
		12.70[.500]	15.24[.600]	12		535542-6
		10.16[.400]	12.70[.500]	10		535542-5
		7.62[.300]	10.16[.400]	8		535542-4
		5.08[.200]	7.62[.300]	6		535542-3
		2.54[.100]	5.08[.200]	4		535542-2
		-	2.54[.100]	2		535542-1
FINISH	B	A	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER		06NOV2002		 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J.OLSON		06NOV02			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.OLSON		06NOV02		NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25022				
	MATERIAL 		APPLICATION SPEC 114-25018		SIZE A2		
FINISH  		WEIGHT -		DRAWING NO C-535542		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1		SHEET 2 of 2	
				REV U5			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-535542-3](#)