



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRODUCTION ISSUE	19JUL2016	KH	AP




AS SUPPLIED

AFTER UNRESTRICTED RECOVERY



SCRAP SECTION A-A



Heat Recoverable screen


Part No.	H		J		P		S REF b	T REF b	U		V REF b	JO REF b	HW ±30% b	JW ±30% b
	MIN	MAX	MIN	MAX	MIN	MAX			MIN	±20%				
	a	b	a	b	a	b			a	b				
222S121-XXC-G28-0	14 {0.55}	10.4 {0.41}	10 {0.39}	5.0 {0.20}	45 {1.77}	31 {1.22}	14 {0.55}	3.0 {0.12}	5.0 {0.20}	10 {0.39}	1.0 {0.04}	15 {0.59}	1.5 {0.06}	1.0 {0.04}
222S132-XXC-G28-0	19 {0.75}	14.2 {0.56}	12 {0.47}	6.0 {0.24}	54 {2.13}	40 {1.57}	16 {0.63}	3.0 {0.12}	5.0 {0.20}	10 {0.39}	1.0 {0.04}	17 {0.67}	1.5 {0.06}	1.0 {0.04}
222S142-XXC-G28-0	25 {0.98}	18.0 {0.71}	14 {0.55}	7.2 {0.28}	63 {2.48}	43 {1.69}	16 {0.63}	3.0 {0.12}	6.0 {0.24}	10 {0.39}	1.0 {0.04}	18 {0.71}	2.0 {0.08}	1.0 {0.04}
222S152-XXC-G28-0	30 {1.18}	22.4 {0.88}	20 {0.79}	8.5 {0.33}	70 {2.76}	50 {1.97}	21 {0.83}	3.0 {0.12}	7.0 {0.28}	12 {0.47}	1.0 {0.04}	20 {0.79}	2.0 {0.08}	1.0 {0.04}
222S163-XXC-G28-0	36 {1.42}	28.2 {1.11}	24 {0.94}	10.0 {0.39}	90 {3.54}	64 {2.52}	26 {1.02}	3.0 {0.12}	12.0 {0.47}	20 {0.79}	1.7 {0.07}	28 {1.10}	2.2 {0.09}	1.5 {0.06}
222S174-XXC-G28-0	43 {1.69}	35.1 {1.38}	32 {1.26}	15.8 {0.62}	111 {4.37}	75 {2.95}	29 {1.14}	3.0 {0.12}	12.0 {0.47}	20 {0.79}	1.7 {0.07}	31 {1.22}	3.0 {0.12}	1.5 {0.06}

DIMENSIONS:

mm[inches]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -



DWN

K. HOLAL

19JUL2016

CHK

N. NAGAR

19JUL2016

APVD

A. POOLE

19JUL2016

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

MATERIAL

-

FINISH

-



TE Connectivity

NAME

135DEG BOOT, COATED

222S1XX-XXC-G28-0

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-

222S1XX-XXC-G28-0

-

SCALE

DNS

SHEET

1 OF 2

REV 1

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - 2017 By - TE Connectivity

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART

Material Dash Number	Material Description	SPEC No.	Coating Slash No.
—3C	POLYOLEFIN/SILVER COMPOSITE	RW-3045	/86, /200
—25C	ELASTOMER/SILVER COMPOSITE	RW-3047	/86, /200
—100C	ZEROHALOGEN/SILVER COMPOSITE	RW-3046	/86, /200

ORDERING INFORMATION

222S1**—**C—G28—0/**



NOTES


- As supplied dimensions are for uncoated parts, when coating is added entry diameters will reduce by 1.5mm Max.
- For method of measuring recovered diameter. see appropriate RW specification (SPEC Number), section 2.2,

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2017 By — TE Connectivity

DIMENSIONS: mm[inches]		DWN K. HOLAL 19JUL2016	MATERIAL —	FINISH —		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK N. NAGAR 19JUL2016	 TE Connectivity			
		APVD A. POOLE 19JUL2016				
		PRODUCT SPEC —			NAME 135DEG BOOT, COATED 222S1XX-XXC-G28-0	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO C-222S1XX-XXC-G28-0	RESTRICTED TO —
		WEIGHT	CUSTOMER DRAWING			
		SCALE DNS		SHEET 2 OF 2		REV 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EK7356-000](#)