


LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED PER ECO-14-006097	24APR14	JR	KR

- 1 WIRE RANGE 0.3-0.82mm2 [22-18 AWG]
- 2 INSULATION RANGE 1.50-3.10 [0.060-1.22]
- 3 FINISH: 0.76um MIN GOLD OVER 1.27um MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4 FINISH: 2.54um MIN PRE-TIN ON ALL SURFACES IN THIS AREA.
- 5 FINISH: 2.54um MIN PRE-TIN ALL OVER
- 6 PRELIMINARY - NOT FOR PRODUCTION



SECTION A-A

SECTION B-B

SECTION C-C

GOLD 3 4	PHOS BRONZE	6 2238021-4
PRE-TIN 5	PHOS BRONZE	6 2238021-3
GOLD 3 4	BRASS	6 2238021-2
PRE-TIN 5	BRASS	2238021-1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.10 [.004]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH

SEE TABLE

DWN
JR RUTH
25FEB14

CHK
K RANDOLPH
25FEB14

APVD
K RANDOLPH
25FEB14

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SOCKET TERMINAL,
VAL-U-LOK, LOOSE PIECE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=2238021

RESTRICTED TO

SCALE
8:1

SHEET
1 OF 1

REV
A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2238021-1](#)