


SPECIFICATION CONTROL DRAWING						SCD		55FB7126																					
Title TWO CONDUCTOR CABLE, SHIELDED, JACKETED, FILTER LINE - ELECTROLOSS						Date 8-17-21		Revision E																					
This specification sheet forms a part of the latest issue of Raychem Specification 55F.																													
COMPONENT WIRE – 55FA0511										SHIELD - TIN-COATED COPPER										JACKET -RADIATION-CROSSLINKED, MODIFIED CONDUCTIVE ETFE									
																													
KEVLAR STRIPPING THREAD																													
CABLE CONSTRUCTION DETAILS										JACKET FLEXURE ENDURANCE MANDREL DIAMETER (in.) (± 3%)																			
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)																						
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM																							
55FB7126-22-*	22	38	.006	.008	.134	.145	16.0	.250																					
55FB7126-20-*	20	38	.006	.008	.150	.161	20.5	.250																					
55FB7126-18-*	18	38	.006	.008	.172	.183	27.8	.250																					
55FB7126-16-*	16	38	.006	.008	.188	.201	34.0	.325																					
55FB7126-14-*	14	38	.007	.009	.224	.237	46.7	.325																					
CABLE RATINGS AND ADDITIONAL REQUIREMENTS																													
TEMPERATURE RATING: 150°C Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level BLOCKING: 200 ± 3°C for 6 hours CROSSLINKING PROOF TEST: 300 ± 3°C for 7 hours FLAMMABILITY: 3 seconds (maximum); 3 inches (maximum); no flaming of facial tissue IDENTIFICATION AND COLOR STRIPING DURABILITY: 125 cycles (250 strokes) (minimum), 500 g weight JACKET COLOR: Black JACKET ELONGATION AND TENSILE STRENGTH: Elongation, 50% (minimum) Tensile Strength, 3500 lbf/in² (minimum) JACKET FLAWS: Not applicable JACKET FLEXURE ENDURANCE: 10 cycles, no cracking LIFE CYCLE: 200 ± 3°C for 168 hours LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours					SOLDERBILITY (Quality Conformance): 95% (minimum) coverage per Mil-STD-202, Method 208 (no steam aging , both conductor and shield) SHIELD COVERAGE: 85% (minimum) VOLTAGE WITHSTAND (Dielectric): Conductor to conductor and shield, 1500 volts (rms), 60 Hz VOLTAGE WITHSTAND (Post Environmental): Not applicable																								
1/ PART NUMBER: The "" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Violet shall be light violet and the designator shall be 7L. Example: AWG 22, light violet and light violet with a blue stripe component wires; black jacket: 55FB7126-22-7L/7L6-0																													
NOTE: Nominal values are for information only. Nominal values are not requirements.																													
Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.																													
1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.																													
Page 1 of 1	Electroloss, Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.					 Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-522-6752																							
	DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL																												
	THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.																												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[55FB7126-22-7L/7L6-0-G171](#)