

SPECIFICATION CONTROL DRAWING

55PC1121

TITLE

TWO CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT


Date

28-Mar-11

Revision

B1

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.



CONSTRUCTION DETAILS									
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1121-28-*	28	38	.0050	.0060	.078	.082	.086	5.33	5.71
55PC1121-26-*	26	38	.0050	.0065	.088	.092	.096	6.86	7.22
55PC1121-24-*	24	38	.0050	.0065	.097	.101	.105	8.55	8.91
55PC1121-22-*	22	38	.0050	.0065	.109	.114	.119	11.10	11.60
55PC1121-20-*	20	38	.0055	.0070	.126	.130	.134	14.95	15.44
55PC1121-18-*	18	38	.0055	.0070	.145	.149	.154	20.40	21.03
55PC1121-16-*	16	38	.0055	.0070	.159	.164	.169	24.81	25.54
55PC1121-14-*	14	38	.0060	.0075	.189	.194	.199	35.52	36.41
55PC1121-12-*	12	38	.0060	.0080	.227	.233	.238	51.71	52.88
55PC1121-10-*	10	36	.0065	.0085	.280	.291	.302	81.65	85.95

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

The TE logo, Tyco Electronics and Raychem are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
 REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



TE Connectivity Wires & Cables
 501 Oakside Avenue
 Redwood City, CA 94063-3800
 Phone: 1-800-227-8816
 Fax: 1-650-361-6297

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWS:

Spark Test, 1000 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

SHIELD COVERAGE: 85% (minimum)

VOLTAGE WITHSTAND TEST (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:

The "" in the part numbers on page 1 shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

1/ Example: AWG 22, red and blue component wires; white jacket:
55PC1121-22-2/6-9

1/ See footer section on page 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[55PC1121-20-0/9-9](#) [55PC1121-20-0/9-9CS2753](#) [55PC1121-22-6/9-9CS2607](#) [55PC1121-16-6/9-9CS2607](#)
[55PC1121-22-0/2-9CS2286](#) [55PC1121-22-4/6-9CS2286](#) [55PC1121-22-9/96-95](#) [55PC1121-12-6/9-9](#) [55PC1121-22-](#)
[6/9-0](#) [55PC1121-12-0/9-9CS2753](#) [55PC1121-16-2/6-9CS2502](#) [55PC1121-18-2/6-9CS2502](#) [55PC1121-18-6/9-](#)
[9CS2607](#) [55PC1121-20-2/6-9](#) [55PC1121-20-2/6-9CS2970](#) [55PC1121-22-94/96-9CS2286](#) [55PC1121-18-9/96-9-L002](#)
[55PC1121-20-9/96-9-L002](#) [55PC1121-22-2/6-9](#) [55PC1121-22-2/6-9CS2970](#) [55PC1121-16-0/9-9CS2753](#) [55PC1121-](#)
[22-0/2-9CS2933](#) [55PC1121-22-94/96-9CS2933](#)