


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - BY - ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		A	INITIAL RELEASE	15NOV2013	YC	BvH
			A1	ECR-14-011671	16AUG2014	GSK	BvH


NOTES:

Tolerances cable lengths:	
0m to 0.5m	+30mm
0.5m to 1.0m	+50mm
1.0m to 3.0m	+100mm
< 3.0m	+1.5%





TECHNICAL DATA	
Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 2 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	8 x 0.25 mm <sup>2</sup>
Wire isolation	PP (br, wh, bl, bk, gr, pk, vi, or)
C-track properties	2 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 7.0 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	−40...+80 °C
Temperature range (mobile)	−20...+80 °C



8 pos	10mtr	PUR	Grey	2273048-4	8x24AWG PUR 10.0m	4
	5mtr			2273048-3	8x24AWG PUR 5.0m	3
	3mtr			2273048-2	8x24AWG PUR 3.0m	2
	1.5mtr			2273048-1	8x24AWG PUR 1.5m	1
	LENGTH”L”	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YATHISH.C 15NOV2013		 TE Connectivity			
		CHK B.VELDHoven 15NOV2013					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME M12 X 1.0 STRAIGHT PLUG PIGT SHLD A			
							
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD A.VAN ZANDVOORT 15NOV2013		SIZE A3 CAGE CODE 00779 DRAWING NO C-2273048 RESTRICTED TO -			
		PRODUCT SPEC 108-19483					
MATERIAL -		FINISH -		APPLICATION SPEC 114-32127			
		WEIGHT -		CUSTOMER DRAWING			
				SCALE NTS		SHEET 1 OF 1	
						REV A1	



NAME	M12 X 1.0 STRAIGHT PLUG PIGT SHLD A
------	-------------------------------------

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2273048	—

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2273048-3](#)