




LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	Z	REV PER 0G3C-0515-04		05JAN05	JR	MM	
	Z1	REVISED PER ECO-09-024927		06NOV09	KK	AEG	

- 1 .000030 GOLD OVER .000030 NICKEL IN CONTACT AREA.
- 2 .000015 GOLD OVER .000030 NICKEL IN CONTACT AREA.
- 3 .067 MAX ALLOWED IN LOCKING POSITION AREA FOR .140 REF LENGTH.
- 4 TIN-LEAD IN CRIMP AREA.
- 5 OBSOLETE
- 6 .000050 GOLD OVER .000050 NICKEL IN CONTACT AREA. REMAINDER OF CONTACT GOLD FLASH OVER NICKEL.
- 7 CRIMP TWIN LEAF CONTACTS WITH 22-18 AWG WIRE RANGE TO BE USED ONLY WITH .125CL & .156CL CRIMP TWIN LEAF HOUSINGS.
- 8 UNPLATED PARTS IN STRIP FORM REELED ON CORRUGATED REEL FOR SALABLE PART.
- 9 TIN IN CRIMP AREA.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	5-583649-3	583649-8	19	105-583649-6
	5-583649-2	583649-9	29	105-583649-5
OBSOLETE	1-583649-1	-	8	-
	583649-4	1-583649-0	6	10583649-7
OBSOLETE	583649-3	583649-8	14	583649-6
OBSOLETE	583649-2	583649-9	24	10583649-5
STRIP PART # STD REELING LEFT TO RIGHT		STRIP PART # REELING RIGHT TO LEFT	FINISH	LOOSE PIECE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

APVD
H ROSE
18FEB94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DWN
A. STAUB BG
18FEB94

CHK
H ROSE
18FEB94

APVD
H ROSE
18FEB94

WEIGHT -

SCALE 10:1

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

CONTACT-TWIN LEAF
(CRIMP-SNAP)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=583649

RESTRICTED TO
-

SHEET 1 OF 1

REV Z1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[583649-6](#)