

4

3

2





1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
BD	39		D	EC 0G3B-0317-03	24APR03	VF GS



1. WIRE RANGE 24-20 AWG.
 2. INSULATION RANGE 1.02-2.03 [.040-.080] DIA.
 3. FOR LOOSE PIECE PART SEE DWG 66594.
- △ 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.
- △ TIN PLATED.
- △ GOLD PLATING PER MIL-G-45204, TIN PER MIL-T-10727
- △ 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA,
1.27μm [.000050] MIN TIN IN LOCALIZED TIN PLATE AREA,
BOTH OVER 1.27μm [.000050] MIN NICKEL.

OBSOLETE	REVERSE REELED FOR MINI-APPLICATOR	△	1-66584-0
	REVERSE REELED FOR MINI-APPLICATOR	△	66584-4
	-	△	66584-3
	REVERSE REELED FOR MINI-APPLICATOR	△	66584-2
	-	△	66584-1
DESCRIPTION		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. FURLER 09JUN2003		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105		
DIMENSIONS: MM [INCHES]		CHK G. STEINHAUER 09JUN03		NAME CONTACT, SOCKET, STRIP TYPE VI, MULTIMATE — —		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. STEINHAUER 09JUN03			
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —			
	MATERIAL BRASS MIL—C—50		APPLICATION SPEC —			
FINISH SEE TABLE		WEIGHT —		SIZE A3		
		CUSTOMER DRAWING		CAGE CODE 00779		
				DRAWING NO C-66584		
				RESTRICTED TO —		
				SCALE 6:1		
				SHEET 1 OF 1		
				REV D		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66584-4](#)