


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


,19

© COPYRIGHT 19 BY AMP INCORPORATED,HARRISBURG,PA. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S.AND FOREIGN PATENTS AND/OR PATENTS PENDING.

MOD	LOC	DIST	P	F	REVISIONS				
13	AJ	16			ZONE	LTR	DESCRIPTION	DATE	APPROVED
						B	REVISED PER AJ-1969.	7-1-86	DH
			✓	✓		C	REV'D PER 0S14-0380-04.	14SEP04	JGH



- 1 COPPER PER ASTM B 152.
- 2 POLYPROPYLENE, GENERAL PURPOSE.
- 3 BRASS PER ASTM B 16.
- 4 BRASS PER ASTM B 36.
- 5 GOLD PLATE PER ASTM B 488.
- 6 TIN PLATE PER ASTM B 545.
- 7 NICKEL PLATE PER QQ-N-290.
- 8. BOARD THICKNESS: .125 MAX.



REQUIRED PCB HOLE CONFIGURATION  
SCALE 8:1

				228435-1	
				PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DEC ± _____ 3 PL DEC ± .002 ANGLES ± _____		DR J. HAVENER 14SEP2004		<div>AMP</div> <div>AMP INCORPORATED Harrisburg, Pa. 17105</div>	
		CHK J. HAVENER 14SEP2004			
		APPD J. HAVENER 14SEP2004			
MATERIAL <div>1 THRU 4</div>		APPD -		NAME JACK, RIGHT ANGLE, PCB, COMMERCIAL SMB	
		PRODUCT SPEC _____			
FINISH <div>5 6 7</div>		APPLICATION SPEC _____		SIZE B	
		WEIGHT _____		FSCM NO 00779	
		SCALE 5:1		DRAWING NO 228435-1	
				SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[228435-1](#)