



2. WIRE RANGE: 0.5–1.4MM² (20–16 AWG).
3. INSULATION RANGE: 2.01–3.20[.079–.126] DIA.

△₄ 0.00076 [.000030] MIN GOLD PER IN
LOCALIZED GOLD PLATE AREA AND 0.00254–0.00635
[.000100–.000250] MATTE TIN IN LOCALIZED TIN
PLATE AREA OVER 0.00127 [.000050] MIN
NICKEL.



SECTION B-B
SCALE 20:1



SECTION A-A
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER		10JAN03		 TE Connectivity	
		CHK C. JONES		10JAN03			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES		NAME	
		0 PLC ± -		PRODUCT SPEC		PIN, MINI UNIVERSAL MATE—N—LOK(TM)	
		1 PLC ± -		—			
		2 PLC ± -		—			
		3 PLC ± 0.13[.005]		APPLICATION SPEC			
		4 PLC ± -		—			
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
—		—		—		—	
CUSTOMER DRAWING				SIZE		CAGE CODE	
				A2		00779	
				DRAWING NO		C-794406	
				SCALE		SHEET	
				10:1		1 OF 1	
				REV		C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[794406-1](#)