





LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C7	PN 2-796638-8 RELEASED FOR PRODUCTION	18MAR2019	RK	PS



796638-3 AS SHOWN



RECOMMENDED PC BOARD LAYOUT

REMOVE PIN 3 8.35±0.15 85	9	-	-	27.22	5	4-796638-1	
	10	-	-	108.50	21	4-796638-0	
		-	-	88.18	17	3-796638-9	
		-	-	72.94	14	3-796638-8	
		-	-	62.78	12	3-796638-7	
		-	-	52.62	10	3-796638-6	
		-	-	47.54	9	3-796638-5	
		-	-	42.46	8	3-796638-4	
		-	-	37.38	7	3-796638-3	
		-	-	32.30	6	3-796638-2	
		-	-	27.22	5	3-796638-1	
		-	-	22.14	4	3-796638-0	
		-	-	17.06	3	2-796638-9	
		-	-	11.98	2	2-796638-8	
		OBSOLETE	9	-	8	42.46	8
6	DETAIL L			52.62	10	2-796638-6	
-	-			128.82	25	2-796638-5	
-	-			123.74	24	2-796638-4	
-	-			118.66	23	2-796638-3	
-	-			113.58	22	2-796638-2	
-	-			108.50	21	2-796638-1	
-	-			103.42	20	2-796638-0	
-	-			98.34	19	1-796638-9	
-	-			93.26	18	1-796638-8	
-	-			88.18	17	1-796638-7	
-	-			83.10	16	1-796638-6	
-	-			78.02	15	1-796638-5	
-	-			72.94	14	1-796638-4	
-	-			67.86	13	1-796638-3	
-	-			62.78	12	1-796638-2	
-	-			57.70	11	1-796638-1	
-	-			52.62	10	1-796638-0	
-	-			47.54	9	796638-9	
-	-			42.46	8	796638-8	
-	-			37.38	7	796638-7	
-	-			32.30	6	796638-6	
-	-			27.22	5	796638-5	
-	-			22.14	4	796638-4	
-	-			17.06	3	796638-3	
-	-			11.98	2	796638-2	
PLATING	MARKING			SPECIAL	DIM L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 190CT2000 S. WELDON CHK 190CT2000 D. BIEVENOUR APVD 190CT2000 D. BIEVENOUR		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME TERM1-BLOK HEADER ASSEMBLY, 90 DEGREE, CLOSED ENDS, 5.08mm PITCH			
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A2		CAGE CODE 00779	
MATERIAL SEE NOTES		WEIGHT -		DRAWING NO C-796638		RESTRICTED TO -	
SEE NOTES		SEE NOTES		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 2
							REV C7

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1. MATERIALS AND FINISH:
HOUSING : PA 6-6, UL 94-V0, COLOR: GREEN.
TERMINAL : COPPER ALLOY, SEE TABLE.

2. MECHANICAL
MAX. INSERTION FORCE PER POLE : 3.0 N
MIN. WITHDRAWAL FORCE PER POLE : 1.5 N
MIN. PC BOARD HOLES DIAMETER : 1.2 mm
MAX. PC BOARD THICKNESS : 2.4 mm

3. ELECTRICAL
WIRE RANGE : 14-30 AWG
MAX. VOLTAGE : 300 V
MAX CURRENT : 11 A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)

4. OPERATING TEMPERATURE RANGE: -40°C TO +105°C

5. NOT CUMULATIVE TOLERANCE.

6. INK MARKED WHITE.

7. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.

8. CONTACTS SELECTIVILY LOADED IN POSITIONS 1,2,4,5,7,8.

9. TIN PLATED WITH 6-7 µm, ALL OVER 2-3 µm NICKEL.

10. PLATED WITH 0.76 µm GOLD ALL OVER 2-3 µm NICKEL.

11. PRELIMINARY - NOT FOR PRODUCTION.

10987654321

DETAIL L

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S. WELDON

19OCT2000

CHK

D. BIEVENOUR

19OCT2000

APVD

D. BIEVENOUR

19OCT2000

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.3
2 PLC	±0.25
3 PLC	±-
4 PLC	±-
ANGLES	±-
FINISH	±-

MATERIAL

SEE NOTES

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV C7

NAME

TERMI-BLOK HEADER ASSEMBLY,
90 DEGREE, CLOSED ENDS,
5.08mm PITCH

SIZE

A2

CAGE CODE

00779

DRAWING NO

796638

RESTRICTED TO

-

TE Connectivity

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[796638-2](#)