

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E3	REVISED PER ECO-11-004587	11MAR2011	RK	HMR
	E4	PART STATUS UPDATED	05JUL2021	SB	SS

D

C

B




A

D

C

B

A



OBSOLETE	0.76µm GOLD	-	-	60.60	55.88	10	2-796859-6
	0.2µm GOLD		DETAIL G	35.20	30.48	5	2-796859-5
	TIN		DETAIL F	25.04	20.32	3	2-796859-4
	TIN	-	-	126.64	121.92	23	2-796859-3
	TIN	-	-	121.56	116.84	22	2-796859-2
	TIN	-	-	116.48	111.76	21	2-796859-1
	TIN	-	-	111.40	106.68	20	2-796859-0
	TIN	-	-	106.32	101.60	19	1-796859-9
	TIN	-	-	101.24	96.52	18	1-796859-8
	TIN	-	-	96.16	91.44	17	1-796859-7
	TIN	-	-	91.08	86.36	16	1-796859-6
	TIN	-	-	86.00	81.28	15	1-796859-5
	TIN	-	-	80.92	76.20	14	1-796859-4
	TIN	-	-	75.84	71.12	13	1-796859-3
	TIN	-	-	70.76	66.04	12	1-796859-2
	TIN	-	-	65.68	60.96	11	1-796859-1
	TIN	-	-	60.60	55.88	10	1-796859-0
	TIN	-	-	55.52	50.80	9	796859-9
	TIN	-	-	50.44	45.72	8	796859-8
	TIN	-	-	45.36	40.64	7	796859-7
	TIN	-	-	40.28	35.56	6	796859-6
	TIN	-	-	35.20	30.48	5	796859-5
	TIN	-	-	30.12	25.40	4	796859-4
	TIN	-	-	25.04	20.32	3	796859-3
	TIN	-	-	19.96	15.24	2	796859-2
TERMINAL PLATING		MARKING	SPECIAL	L	H	NO. OF POSN	PART NUMBER

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
TERMINAL: PHOSPHOR BRONZE, PLATING: SEE TABLE, OVER 2-3µm NICKEL
2. SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE No. E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE ON CONFORMITY WITH IEC 998-1/998-2-1.
5. INK MARKING, COLOR: WHITE.
6. LABEL APPLIED OR INK MARKING AS SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±0.00
3 PLC ±0.000
4 PLC ±0.0000
ANGLES ±
FINISH

DWN S. WELDON 12FEB2001
CHK D. BIEVENOUR 12FEB2001
APVD D. BIEVENOUR 12FEB2001

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK, PLUG
90 DEGREE, WITH FLANGE,
5.08mm PITCH

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-796859

RESTRICTED TO

SCALE 4:1
SHEET 1 OF 2
REV E4

4


3

2


1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DETAIL F



DETAIL G

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.2

2 PLC ±0.00

3 PLC ±0.000

4 PLC ±0.0000

ANGLES ±

FINISH

DWN S.WELDON 12FEB2001

CHK D.BIEVENOUR 12FEB2001

APVD D.BIEVENOUR 12FEB2001

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TERMINAL BLOCK, PLUG
90 DEGREE, WITH FLANGE,
5.08mm PITCH

A200779

C-796859

SCALE 4:1

SHEET 2 OF 2

REV E 4

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-796859-3](#)