




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	6-2-17	CT	DH



- 1 "TE", TE PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN. PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2 MATERIAL: HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC, BLACK, UL94 V-0
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
LOW POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3 CONTACT PLATING: SIGNAL CONTACTS - .000050 MIN Ni UNDER ALL
.000050 MIN Au ON CONTACT AREA
.000005 MIN Au AT PCB INTERFACE
POWER CONTACTS - .000050 MIN Ni UNDER ALL
.000050 MIN Au ON CONTACT AREA
.000005 MIN Au AT PCB INTERFACE
LOW POWER CONTACTS - .000050 MIN Ni UNDER ALL
.000050 MIN Au ON CONTACT AREA
.000005 MIN Au AT PCB INTERFACE
- 4 MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7 PCB - .0453 $\pm$.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 DIA HOLE.



2ACP + 1LP + 32S + 3HDP + 1LP + 1HDP	2317477-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 3-17-17	TE Connectivity	
DIMENSIONS: INCHES		CHK D. HOANG 3-17-17		
		APVD D. HOANG 3-17-17	NAME RIGHT ANGLE HEADER ASSEMBLY W/LP CONTACT WITH GUIDELESS MULTI BEAM XLE	
		PRODUCT SPEC 108-2292		
MATERIAL : 2		APPLICATION SPEC 114-13251	SIZE A100779	
		FINISH : 3		
CUSTOMER DRAWING		WEIGHT -	RESTRICTED TO -	
SCALE 2:1		SHEET 1 OF 2		REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2317477-1](#)