


LOC —	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			E	Contact pin base material change from CuSn (Phosphor bronze)to CuZn (Brass). Plating change from MIN. 0.8µm gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).	22JUL2014	TJ	JK	

VERWENDET FÜR
E 88-52 549

POLZ. PRO REIHE	L±0.4	BESTELL-NR.
—	—	—
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	3 — -6
7	17.78	— -7
8	20.32	2 — -8
9	22.86	3 — -9
10	25.40	2 1 — -0
11	27.94	3 1 — -1
12	30.48	1 — -2
13	33.02	2 1 — -3
14	35.56	3 1 — -4
15	38.10	2 1 — -5
16	40.64	1 — -6
17	43.18	1 — -7
18	45.72	3 1 — -8
19	48.26	3 1 — -9
20	50.80	2 — -0
21	53.34	2 — -1
22	55.88	3 2 — -2
23	58.42	2 — -3
24	60.96	3 2 829192 4
25	63.50	2 — -5
26	66.04	2 — -6
27	68.58	3 2 — -7
28	71.12	2 — -8
29	73.66	3 2 — -9
30	76.20	3 — -0
31	78.74	3 3 — -1
32	81.28	3 3 — -2
33	83.82	3 3 — -3
34	86.36	3 3 — -4
35	88.90	3 3 — -5
36	91.44	3 3 — -6
37	93.98	3 3 — -7
38	96.52	3 3 — -8
39	99.06	3 3 — -9
40	101.60	4 — -0
41	104.14	3 4 — -1
42	106.68	3 4 — -2
43	109.22	3 4 — -3
44	111.76	3 4 — -4
45	114.30	3 4 — -5
46	116.84	4 — -6
47	119.38	3 4 — -7
48	121.92	3 4 — -8
49	124.46	3 4 — -9
50	127.00	2 5 — -0

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH

- △1 STECKSEITE: IM BEREICH "F" 0.7µm PdNi+0.1µm GOLD FLASH
ÜBER 1.27µm NICKEL
LÖTSEITE: MIN. 2.5µm ZINN ÜBER 1.27µm NICKEL
- △2 OBSOLETE
- △3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



KONTAKTSTIFT	CuZn	△1
STIFTGEHÄUSE	PBT	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE
		FARBE

ZEICHNUNG GÜLTIG AB KW 26/90

DIMENSIONS: mm	DWN A.HO	28.09.88	MATERIAL	SEE TABLE	FINISH	SEE TABLE
	CHK M.SCHAARSCHMIDT	28.09.88				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	—				
0 PLC ±0.2 mm	PRODUCT SPEC	108-18012	NAME SPEZ. AMPMODU II STIFTELEISTE ZWEIREIHIG LOW COST LINE			
1 PLC ± —	APPLICATION SPEC	—				
2 PLC ± —	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC ± —			A4	00779	C-829192	—
4 PLC ± —						
ANGLES ± —						
CUSTOMER DRAWING				SCALE	4:1	SHEET 1 OF 1
						REV E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-829192-6](#)