

LOC		DIST		REVISIONS					
P	LTR	DESCRIPTION		DATE	DWN	APVD			
		WAR NR. 3-88-9833-0		F	Plating change from MIN. 0.8µm gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).		30SEP2014	PS	JK
PASSEND ZU PROJ.-NR. E 90-52554									

POLZ. PRO REIHE	L±0.4	BESTELL-NR.	
-	-	-	-
2	5.08	-	2
3	7.62	-	3
4	10.16	-	4
5	12.70	-	5
6	15.24	-	6
7	17.78	-	7
8	20.32	-	8
9	22.86	-	9
10	25.40	1-	-0
11	27.94	1-	1
12	30.48	1-	2
13	33.02	1-	3
14	35.56	1-	4
15	38.10	1-	5
16	40.64	1-	6
17	43.18	1-	7
18	45.72	1-	8
19	48.26	1-	9
20	50.80	2-	-0
21	53.34	2-	1
22	55.88	2-	2
23	58.42	2-	3
24	60.96	2-	4
25	63.50	2-	5
26	66.04	2-	6
27	68.58	2-	7
28	71.12	2-	8
29	73.66	2-	9
30	76.20	3-	829587-0
31	78.74	3-	1
32	81.28	3-	2
33	83.82	3-	3
34	86.36	3-	4
35	88.90	3-	5
36	91.44	3-	6
37	93.98	3-	7
38	96.52	3-	8
39	99.06	3-	9
40	101.60	4-	0
41	104.14	4-	1
42	106.68	4-	2
43	109.22	4-	3
44	111.76	4-	4
45	114.30	4-	5
46	116.84	4-	6
47	119.38	4-	7
48	121.92	4-	8
49	124.46	4-	9
50	127.00	5-	-0

KONTAKT	WERKSTOFF	OBERFLÄCHE
CuSn	PBT	GRÜN
BENENNUNG	WERKSTOFF	FARBE

DIMENSIONS:		DWN	17.04.90	MATERIAL	SEE TABLE	FINISH	SEE TABLE
mm		A.HO	-	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	M.SCHAARSCHMIDT	SPEZIAL AMPMODU II STIFTLEISTE			
±0.2 mm		APVD	-	ZWEIREIHIG			
0 PLC ± -		PRODUCT SPEC	108-18012	NAME			
1 PLC ± -		APPLICATION SPEC	-	SIZE			
2 PLC ± -		WEIGHT	-	CAGE CODE			
3 PLC ± -				DRAWING NO			
4 PLC ± -				RESTRICTED TO			
ANGLES ± -				A4 00779 C-829587			


CUSTOMER DRAWING	SCALE	SHEET	1 OF 1	REV	F
	4:1				

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - By -



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-829587-0](#)