



REVISIONS				DATE	APPROVED
P	F	ZONE	LTR		
		F2		31MAR11	HMR
DESCRIPTION				REVISED PER ECO-11-005140	



① WILL ALSO MATE W/OTHER CONNECTORS WHICH ARE COMPATIBLE WITH THE .040 & .150 END DIMS.

② OBSOLETE PART NUMBER

③ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3	OBSOLETE	3.132	3.032	2.806	.106	2.890	.190	3.804	3.604	3.200	2.900	29	60	2-87496-6
		3.032	2.932	2.706		2.790		3.704	3.504	3.100	2.800	28	58	2-87496-5
		2.932	2.832	2.606		2.690		3.604	3.404	3.000	2.700	27	56	2-87496-4
		2.832	2.732	2.506		2.590		3.504	3.304	2.900	2.600	26	54	2-87496-3
		2.732	2.632	2.406		2.490		3.404	3.204	2.800	2.500	25	52	2-87496-2
		2.632	2.532	2.306		2.290		3.304	3.104	2.700	2.400	24	50	2-87496-1
		2.532	2.432	2.206		2.190		3.204	3.004	2.600	2.300	23	48	2-87496-0
		2.432	2.332	2.106		2.090		3.104	2.904	2.500	2.200	22	46	2-87495-9
		2.332	2.232	2.006		2.090		3.004	2.804	2.400	2.100	21	44	2-87495-8
		2.232	2.132	1.906		1.990		2.904	2.704	2.300	2.000	20	42	2-87495-7
3	OBSOLETE	2.132	2.032	1.806		1.890		2.804	2.604	2.200	1.900	19	40	2-87495-6
		2.032	1.932	1.706		1.790		2.704	2.504	2.100	1.800	18	38	2-87495-5
		1.932	1.832	1.606		1.690		2.604	2.404	2.000	1.700	17	36	2-87495-4
3	OBSOLETE	1.832	1.732	1.506		1.590		2.504	2.304	1.900	1.600	16	34	2-87495-3
		1.732	1.632	1.406		1.490		2.404	2.204	1.800	1.500	15	32	2-87495-2
3	OBSOLETE	1.632	1.532	1.306		1.390		2.304	2.104	1.700	1.400	14	30	2-87495-1
		1.532	1.432	1.206		1.290		2.204	2.004	1.600	1.300	13	28	2-87495-0
3	OBSOLETE	1.432	1.332	1.106		1.190		2.104	1.904	1.500	1.200	12	26	2-87494-9
		1.332	1.232	1.006		1.090		2.004	1.804	1.400	1.100	11	24	2-87494-8
		1.232	1.132	.906		.990		1.904	1.704	1.300	1.000	10	22	2-87494-7
		1.132	1.032	.806	.106	.890	.190	1.804	1.604	1.200	.900	9	20	2-87494-6
		1.032	.932	—	.406	—	.490	1.704	1.504	1.100	.800	8	18	2-87494-5
		.932	.832	—	.306	—	.390	1.604	1.404	1.000	.700	7	16	2-87494-4
		.832	.732	—	.206	—	.290	1.504	1.304	.900	.600	6	14	2-87494-3
		.732	.632	—	.106	—	.190	1.404	1.204	.800	.500	5	12	2-87494-2
		.632	.532	—	.006	—	.090	1.304	1.104	.700	.400	4	10	2-87494-1
		2.632	2.532	2.306	.106	2.390	.190	3.304	3.104	2.700	2.400	24	50	87496-1
		L	K	J	H	G	F	E	D	C	B	A	NO. OF POS.	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±.005
ANGLES ±

MATERIAL
WSG. - GLASS FILLED NYLON
COLOR: BLACK
POST - PHOS. BRONZE
FINISH
POST - .00030 GOLD OVER
.00050 NICKEL

CONTRACT NO

DR *D. J. J. 8/21/75*

CHK *D. J. J. 8-22-75*

APPD *B. Bennett 8/25/75*

APPD *R. Clark 8/25/75*

DSGN APPD

OTHER APPD

TE TE Connectivity

NAME

HEADER ASSY. MOD II .100x.100
CENTERS WITH PIN. PROTECTION
BOTH SIDES & MTG. EARS
(MATES W/AMP LATCH OR FCC ONE SIDE) ①
& MOD IV OTHER SIDE

SIZE CODE IDENT NO DRAWING NO

C

00779

87496

SCALE

SHEET

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[87496-7](#)