



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECR-18-014960	21SEP2018	SS	JL
	A1	REVISED PER ECR-19-008871	13JUN2019	SR	DD
	A2	REVISED PER ECR-19-009651	12JUL2019	SR	DD
	B	REVISED PER ECR-19-017691	19NOV2019	SB	DD


1. MATERIALS:
HOUSING: PBT
DIMMING CONTACTS (QTY. 4): COPPER ALLOY
LINE VOLTAGE CONTACTS (QTY. 3): COPPER ALLOY
GASKET: VINYL/NITRILE FOAM
O-RING: SILICONE RUBBER
MEMBRANE VENT: PTFE
 2. FINISH:
DIMMING CONTACTS: NICKEL UNDERPLATE ENTIRE
CONTACT 0.127 μ m MIN THICK. SELECTIVE GOLD PLATE CONTACT
MATING AREA (MATING FACE SIDE ONLY) 0.76 μ m MIN THICK.
MATTE TIN PLATE TAB ON BOTH SIDES 0.30 μ m MIN THICK.
LINE VOLTAGE CONTACTS: MATTE TIN PLATE
 3. MATING INTERFACE PER ANSI C136.41-2013.
 4. ADHESIVE BACKED GASKET SUPPLIED BUT NOT INSTALLED.
 5. ADDITIONAL COVERS AND SLEEVES OF VARIOUS HEIGHTS ARE
AVAILABLE. CONTACT TE CONNECTIVITY FOR MORE OPTIONS.
7. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.




2336396-1 SHOWN





1 - 2336396 - 1 SHOWN



2336396-2 SHOWN






1-2336396-2 SHOWN



2213996-X	2306130-X	5	13.04	26.20	Ø82.24	Ø78.54	Ø69.80	Ø70.70	Ø72.25	Ø77.53	Ø77.74	Ø81.15	1-2336396-2
2213996-X	2306130-X	7	13.04	26.20	Ø82.24	Ø78.54	Ø69.80	Ø70.70	Ø72.25	Ø77.53	Ø77.74	Ø81.15	2336396-2
2213805-X	2213748-X	5	4.35	27.45	Ø77.00	Ø73.00	Ø64.50	Ø65.00	Ø66.75	Ø71.23	Ø72.00	Ø76.00	1-2336396-1
2213805-X	2213748-X	7	4.35	27.45	Ø77.00	Ø73.00	Ø64.50	Ø65.00	Ø66.75	Ø71.23	Ø72.00	Ø76.00	2336396-1
REPRESENTATIVE SLEEVE P/N 	REPRESENTATIVE COVER P/N 	CONTACT POSITIONS	DIM T	DIM S	DIM Y	DIM X	DIM P	DIM N	DIM M MAX WITH SLEEVE	DIM M MAX W/OUT SLEEVE	DIM F	DIM E	PART NO.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 03MAY2018		 TE Connectivity	
		CHK M. MOSTOLLER 03MAY2018			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME BASE ASSEMBLY, LIGHT CONTROLLER, SLEEVE COMPATIBLE	
		PRODUCT SPEC 108-32125			
		APPLICATION SPEC 114-32159			
MATERIAL		WEIGHT			
-  - 		- 		SIZE A2	
				CAGE CODE -	
				DRAWING NO C-2336396	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 2:1 SHEET 1 OF 5 REV B	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 03MAY2018	TE Connectivity			
DIMENSIONS:		CHK M. MOSTOLLER 03MAY2018				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME BASE ASSEMBLY, LIGHT CONTROLLER, SLEEVE COMPATIBLE			
	0 PLC ±-	PRODUCT SPEC	SIZE A2			
	1 PLC ±0.2	108-32125	CAGE CODE -			
	2 PLC ±0.13	APPLICATION SPEC	DRAWING NO C-2336396			
	3 PLC ±-	114-32159	RESTRICTED TO -			
MATERIAL	4 PLC ±-	WEIGHT	SCALE 2:1			
-	ANGLES ±3°	-	SHEET 2 OF 5			
-	FINISH	CUSTOMER DRAWING	REV B			


		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB
SCALE 3:2




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03MAY2018 J. SHAFFER		 TE Connectivity	
		CHK 03MAY2018 M. MOSTOLLER			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.2 1 PLC ±0.13 2 PLC ±.13 3 PLC ±. 4 PLC ±. ANGLES ±3°		NAME BASE ASSEMBLY, LIGHT CONTROLLER, SLEEVE COMPATIBLE	
		PRODUCT SPEC 108-32125		SIZE A2	
MATERIAL - -		APPLICATION SPEC 114-32159		CAGE CODE -	
FINISH - -		WEIGHT -		DRAWING NO C-2336396	
CUSTOMER DRAWING				SCALE 2:1	SHEET 3 of 5
				REV B	



MATING COVER DIMENSIONS
FOR
76MM DIAMETER BASES
(2336396-1, 1-2336396-1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 03MAY2018	 TE Connectivity			
		CHK M. MOSTOLLER 03MAY2018				
DIMENSIONS:		APVD -	NAME BASE ASSEMBLY, LIGHT CONTROLLER, SLEEVE COMPATIBLE			
mm		PRODUCT SPEC 108-32125				
		APPLICATION SPEC 114-32159	SIZE A2	CAGE CODE -	DRAWING NO C-2336396	RESTRICTED TO -
MATERIAL		WEIGHT -				
		CUSTOMER DRAWING	SCALE 2:1	SHEET 4	OF 5	REV B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



MATING COVER DIMENSIONS
FOR
81MM DIAMETER BASES
(2336396-2, 1-2336396-2)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 03MAY2018	TE Connectivity			
		CHK M. MOSTOLLER 03MAY2018				
DIMENSIONS:		APVD -	NAME BASE ASSEMBLY, LIGHT CONTROLLER, SLEEVE COMPATIBLE			
mm		PRODUCT SPEC 108-32125	SIZE A2		CAGE CODE -	
		APPLICATION SPEC 114-32159	DRAWING NO C-2336396		RESTRICTED TO -	
MATERIAL		WEIGHT -	SCALE 2:1		SHEET 5 OF 5	
		CUSTOMER DRAWING			REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2336396-1](#)