






SECTION A-A

1 KODIERUNG ZW ISCHEN KAMMER 1 UND 2 DARGESTELLT (AUF ANFRAGE)
KEYING SHOWN BETWEEN CAVITY 1 AND 2 (ON REQUEST)

2 RASTHAKEN BEI ERSTER UND LETZTER KAMMER IMMER VORHANDEN
LOSCKING CLIP ALWAYS ON FIRST AND LAST CAVITY

3 ZUSATZLICHE RASTHAKEN ZWISCHEN KAMMER-NR.SIEHE BLATT 2 VON 2
ADDITIONAL LOCKING CLIP BETWEEN CAVITY NO SEE SHEET 2 OF 2

4 KAMMERNUMMER
CAVITY NO

5 RASTFENSTER IMMER VORHANDEN
LOCKING WINDOW ALWAYS PRESENT

6 LEITERPLATTE VORZUGSWEISE ANGEFAST
PCB CHAMFERED PREFERABLE

7 PLATZBEDARF FOR RAHMEN
AREA FOR FRAME

8 PR ÜF ÖFFNUNGEN
INSPECTION HOLES

9 KLEMMFEDERN NIGHT VOL AUSGESDPRITZTE KONTUR ZUL ßSSIG
CLIPS.SHAPE NOT FULLY MOLDED PERMISSIBLE

10 Passende Gegenstecker siehe PN 829 868/966 194
MATING PARTS SEE PN 829 868/966 194

12 WITH STROKE LINE DRAWN VERSIONS NOT YET AVAILABLE

13 14 15 SIEHE BLATT 2 VON 2
SEE SHEET 2 OF 2



16 Aubennuten eingeengt.
Varianten eiehe Blatt 2)
GROOVES ON OUTSIDE NARROWED.VERSIONS SEE SHEET 2

17 GLOW WIRE TEST 750°C ACC.DIN EN 60695-2-11
WITHOUT FLAME

18 OBSOLETE

19 PRELIMINARY PART, NOT FOR PRODUCTION

20 HOOK DIMENSION, NOT THE DIMENSION FOR MIDDLE WALL



WIRE DIRECTION

TOLERANCE NOT SPECIFIED ±0.1


20	49.5	52.6	47.5	-															1-	C version (all PNs)	964576-0
19	47	50.1	45.0	-														1- ¹⁸	964576-9		
18	44.5	47.6	42.5	-														1-	964576-8		
17	42	45.1	40.0	-													2-	1-	964576-7		
16	39.5	42.6	37.5	-														1-	964576-6		
15	37	40.1	35.0	-													2- ¹⁸	1-	964576-5		
14	34.5	37.6	32.5	-														1-	964576-4		
13	32	35.1	30.0	-														1- ¹⁸	964576-3		
12	29.5	32.6	27.5	-					6- ¹⁸	5-	4- ¹⁸	3-	2-	1- ¹⁸					964576-2		
11	27	30.1	25.0	-														2-	1-		964576-1
10	24.5	27.6	22.5	-									3- ¹⁸	2-	1- ¹⁸				964575-0		
9	22	25.1	20.0	-										2-	1-					964575-9	
9	22	25.1	20.0	-	9-															A	964575-9 ¹⁷
8	19.5	22.6	17.5	-	9-															A	964575-8 ¹⁷
8	19.5	22.6	17.5	-														2-	1-	C	964575-8
7	17	20.1	15.0	-	9-	8- ¹⁹														A	964575-7 ¹⁷
7	17	20.1	15.0	-									4- ¹⁸	3-	2-	1-				C	964575-7
6	14.5	17.6	12.5	-										3-	2-	1-				C	964575-6
5	12	15.1	10.0	-	9-	8-	7-													A	964575-5 ¹⁷
5	12	15.1	10.0	-										4-	3- ¹⁸	2-	1-			C	964575-5
4	9.5	12.6	7.5	-	9- ¹⁹															C	964575-4 ¹⁷
4	9.5	12.6	7.5	-										4- ¹⁸	3-	2-	1-			C	964575-4
3	7	10.1	5.0	-	9-													2- ¹⁸	1-	C	964575-3
3	7	10.1	5.0	-									4-							C	964575-3 ¹⁷
3	7	10.1	5.0	-		8-	7-							3-						A	964575-3 ¹⁷
POS	DIM C	DIM B	DIM A		KEYING VERSIONS SEE SHEET 2 OF 2															REV	HOUSING PART NO

KEYING VERSIONS SEE SHEET 2 OF 2

REV

HOUSING PART NO

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE INFORMATION CONTAINED HEREIN IS NOT TO BE USED FOR ANY OTHER PURPOSES WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		DWG: ATZMANN 06JULY2019 CHK: BORMUTH 06JULY2019 APVD: -	TE CONNECTIVITY	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME: AMP DUOPLUG 2.5 SYSTEM PCB RAHMEN AMP DUOPLUG 2.5 SYSTEM PCB FRAME (3-20 Posn)
0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±0.1		PRODUCT SPEC APPLICATION SPEC		SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO: -
MATERIAL: PA 6.6 25%GF UL94 V-0		WEIGHT: -		SCALE: 10:1
CUSTOMER DRAWING		SHEET 1 OF 2		REV: 20



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-964575-8](#)